



SKU # H11-5K-G6v2

Part # 1007007

Description

GEN6v2 H11 5,500 Kelvin Canbus Quick Start HID SLIM 99% Plug-&-Play Kit with Lifetime Warranty

Categories HID Headlight Conversions

Sub-Categories Gen6v2 CANBUS HID Headlight Kit

UPC 817999026078

Unit of Measure Kit

Related Skus:

Cross Sell Skus:

Condition

New

Manufacturer

Race Sport Lighting

EZ Category

GEN6v2 Lifetime HID Kits

Harmonization Code

8512.20.2080

Universal

YES

Life Expectancy

30,000 hours

SEMA Product

Headlight Conversion Kit

Part Type ID 12571

Reverse Polarity

Headlight Conversion Kit

Operating Voltage

Current Draw

Wattage

35-Watts

Chip Type

XENON HID

IP Rating

IP67

LUX

Kelvin (ColorTemperature)

5,000K

Universal or Vehicle Specific

Universal

Made In

China

Warranty

Lifetime

Lumens

Beam Pattern

N/A



Product Information

You thought the GEN6® was the greatest headlight kit on the HID headlight market? You were right! But now the GEN6v2 gives you all that plus Quick Fire Bulbs! Get all the benefits of the GEN® HID kits, but now with the following: - Lifetime Warranty on bulb and ballasts. Not just the ballast. -Quick Start HID Bulbs (Faster than standard HID bulbs on ignition) -Shielded cable on the bulb wires to match the GEN6® ballasts. This King of HID Kits gives you the following benefits in summary: -Lifetime warranty on both bulbs and ballasts -Quick Fire HID bulbs -CANBUS circuitry to interfaces with 99.9% of cars without the need for relay harnesses -Radio interference shielding -Shielded wire cables -and more... -TECH NOTE - DO NOT USE ON MOPAR VEHICLES LIKE DODGE, JEEP AND CHRYSLER. PLEASE ONLY USE THE ORIGINAL GEN6® HID KITS TO PUT IN THOSE VEHICLES. THE G6V2 KITS HAVE A VOLTAGE LEVEL THAT DOES NOT INTERFACE PROPERLY WITH THE MOPAR PLATFORM. (Highly recommended for Projector style len

Est. Labor	1 Hours	Width	7.50
Gross Weight	3.20	Height	3.75
Net Weight	3.20	Depth	10.00
DIM Weight	2.02		

Prop 65 WARNING: This product can expose you to chemicals, which are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov