



Product Family Uvex Skyper

Wrap-around protective eyewear offers exceptional comfort, protection and fit. Adjustable temple length and lens inclination.

[Learn more about all of our Uvex plano products at **uvex.us** >](#)

[Learn more about our Uvex Rx safety frames at **uvexrx.com** >](#)



Product Numbers & Ordering Information

	Product Numbers	Details
	S1900-BR	Black Frame Clear Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1900X-BR	Black Frame Clear Lens, Uvextreme Anti-fog Coating. CA 18,832
	S1901-BR	Black Frame Espresso Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1901X-BR	Black Frame Espresso Lens, Uvextreme Anti-fog Coating. CA 18,832
	S1902-BR	Black Frame Amber Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1903-BR	Black Frame SCT-Gray Lens, Uvextreme Anti-fog Coating
	S1904X	Black Frame SCT-Gray Lens, Uvextreme Anti-fog Coating

Uvex Skyper

	S1903	Black Frame Gold Mirror Lens, Ultra-dura Anti-scratch Coating
	S1904X-BR	Black Frame Gold Mirror Lens, Ultra-dura Anti-scratch Coating
	S1905-BR	Black Frame SCT-Reflect 50 Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1907-BR	Black Frame Shade 3.0 Infra-dura Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1908-BR	Black Frame Shade 5.0 Infra-dura Lens, Ultra-dura Anti-scratch Coating. CA 18,832
	S1934X-BR	Black Frame Gray Lens, Uvextreme Anti-fog Coating. CA 18,832
	S1900	Black Frame Clear Lens, Ultra-dura Anti-scratch Coating
	S1900X	Black Frame Clear Lens, Uvextreme Anti-fog Coating
	S1901	Black Frame Espresso Lens, Ultra-dura Anti-scratch Coating
	S1901X	Black Frame Espresso Lens, Uvextreme Anti-fog Coating
	S1902	Black Frame Amber Lens, Ultra-dura Anti-scratch Coating
	S1905	Black Frame SCT-Reflect 50 Lens, Ultra-dura Anti-scratch Coating
	S1906	Black Frame Shade 2.0 Infra-dura Lens, Ultra-dura Anti-scratch Coating

Uvex Skyper

	S1907	Black Frame Shade 3.0 Infra-dura Lens, Ultra-dura Anti-scratch Coating
	S1908	Black Frame Shade 5.0 Infra-dura Lens, Ultra-dura Anti-scratch Coating
	S1930X	Black Frame SCT-Low IR Lens, Uvextreme Anti-fog Coating
	S1931X	Black Frame SCT-Vermilion Lens, Uvextreme Anti-fog Coating
	S1932X	Black Frame SCT-Blue Lens, Uvextreme Anti-fog Coating
	S1933X	Black Frame SCT-Orange Lens, Uvextreme Anti-fog Coating
	S1934X	Black Frame Gray Lens, Uvextreme Anti-fog Coating
	S6500	Replacement Lens Clear, Ultra-dura Anti-scratch Coating
	S6500-BR	Replacement Lens Clear, Ultra-dura Anti-scratch Coating
	S6500X	Replacement Lens Clear, Uvextreme Anti-fog Coating
	S6500X-BR	Replacement Lens Clear, Uvextreme Anti-fog Coating
	S6501	Replacement Lens Espresso, Ultra-dura Anti-scratch Coating
	S6501-BR	Replacement Lens Espresso, Ultra-dura Anti-scratch Coating

	S6502	Replacement Lens Amber, Ultra-dura Anti-scratch Coating
	S6502-BR	Replacement Lens Amber, Ultra-dura Anti-scratch Coating
	S6503	Replacement Lens Gold Mirror, Ultra-dura Anti-scratch Coating
	S6503-BR	Replacement Lens Gold Mirror, Ultra-dura Anti-scratch Coating
	S6504X	Replacement Lens SCT-Gray, Uvextreme Anti-fog Coating
	S6504X-BR	Replacement Lens SCT-Gray, Uvextreme Anti-fog Coating
	S6501X	Replacement Lens Espresso, Uvextreme Anti-fog Coating
	S6505	Replacement Lens SCT-Reflect 50, Ultra-dura Anti-scratch Coating
	S6506	Replacement Lens Shade 2.0 Infra-dura, Ultra-dura Anti-scratch Coating
	S6507	Replacement Lens Shade 3.0 Infra-dura, Ultra-dura Anti-scratch Coating
	S6508	Replacement Lens Shade 5.0 Infra-dura, Ultra-dura Anti-scratch Coating
	S6509X	Replacement Lens SCT-Low IR, Uvextreme Anti-fog Coating
	S6512X	Replacement Lens Gray, Uvextreme Anti-fog Coating

Packaging Information

Packaging: Ind. box, 10/stocker, 200/case

Overview

Key Features

Wrap-around protective eyewear offers exceptional comfort, protection and fit

- Easy and economical lens replacement system
- Adjustable temple length and lens inclination
- Lifetime frame guarantee
- Made in USA

Hazards

- Abrasion
- Airborne Particulates
- Biohazard
- Electrical & Arc
- Impact
- Low Visibility

Regulations

- ANSI Z87+ - Meets ANSI Z87+ (High Impact) standard
- ANSI Z.87.1/1989, CA 18,832 - Meets ANSI Z.87.1/1989, CA 18,832 (http://www.mte.gov.br/Empregador/segsau/Pesquisa/CA_DET.asp?VNRCAProc=18832&Equipamento=00&NOEquipamento=&Fabricante=00&NOFabricante=)
- CSA Z94.3 - Tested by Honeywell to meet the requirements of the CSA Z94.3 standard
- Military V0 - Meets military V0 ballistic test for impact

Historical Brand

Uvex

Warranty Information

Lifetime frame guarantee

Specifications

Lens overall width

- 142 mm (5.5) nominal "

Lens material

- Polycarbonate

Lens coating

- Ultra-dura,® Uvextreme® AF

Lens thickness

- 2 mm (.079) minimum "

Available lens tints

- Clear, Espresso, Amber, Gold Mirror, SCT-Gray, SCT-Reflect 50, Shade 2.0, Shade 3.0, Shade 5.0, SCT-Low IR, SCT-Vermilion, SCT-Blue, SCT-Orange, Gray

Replacement lenses available (yes/no)

- Yes

Rx capable

- No

Temple material

- Nylon

Temple length

- 130-145 mm (5.5-5.8") "

Temple set-back

- 100 mm (4.0) nominal "

Temple style

- Duoflex® cushioned

Spectacle weight

- 32 grams (1 oz.) approx.

Frame material

- Texin

Available frame colors

- Black

Dielectric frame (yes/no)

- Yes

Country of origin

- Made in U.S.A

Certifications

ANSI Certificate of Compliance_Eng

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Laser_Filters___Eyewear/19294/1033.aspx

ANSI Certificate of Compliance_Eng

ANSI Certificate of Compliance_Spanish

http://www.honeywellsafety.com/Supplementary/Documents_and_Downloads/Eye_and_Face_Protection/Laser_Filters___Eyewear/19295/1033.aspx

ANSI Certificate of Compliance_Spanish

Training & Proper Use

All products come packaged with instructions and warnings for proper use.

Technical Support

(800) 682-0839, Sperian Protection Americas, Customer Care