



VS3 SAFETY EYEWEAR
SERIES VS
SPECIFICATION SHEET



PRODUCT FEATURES:

- Stylish single wrap around lens
- Brow guard
- Soft rubberized nose bridge for comfort and to prevent slippage
- Rubberized temples for secure fit
- Hard coated lens prevents scratches
- Anti-Fog lens
- Clear and tinted lenses available
- 99.9% UV Protection
- OSHA compliant

TECHNICAL DATA:

- Lens Material: Polycarbonate
- Lens Vertical Length: 1.75"
- Lens Horizontal Length: 3.00"
- Lens Thickness: 3 mm
- Overall Length: 7.00"
- Overall Width: 6.00"
- Weight: 0.0048 lbs.
- Lens: Hard Coated, Anti-Fog, Anti-Scratch
- Nose Bridge: Silicone Rubber
- Temples: Rubberized
- Size: Universal
- COO: China

STANDARDS & COMPLIANCE:

- ANSI Z87+
- CE EN 166
- OSHA Compliant

APPLICATIONS & CARE:

The VS3 Safety Eyewear can be worn in many environments such as manufacturing, construction, scientific, industrial, healthcare, education, woodworking and many more. They are lightweight and provide all day comfort.

VS3 Safety eyewear may be cleaned with soap and warm water then dried with a soft lint free cloth. One can use microfiber or a dry cloth made for eyewear to clean the lens. Do not clean with any harsh chemicals, gas, or an abrasive cleaner. The eyewear should be stored away from direct sunlight and from chemicals. Do not expose to extreme temperatures.



Packaging and Logistics Information

SKU	LENS COLOR	FRAME COLOR	ANTI-FOG	CASE QTY	CASE WT	UPC
OF-VS3-05	Clear	Black	Yes	100 PC	12.8 lbs.	069165845635
		Orange				
OF-VS3-85	Tinted	Black	Yes	100 PC	12.8 lbs.	069165846465
		Orange				
OF-VS3-06	Clear	Black	Yes	100 PC	12.8 lbs.	069165846410
OF-VS3-86	Tinted	Black	Yes	100 PC	12.8 lbs.	069165846472
OF-VS3-07	Clear	Safety Yellow	Yes	100 PC	12.8 lbs.	069165846489
OF-VS3-87	Tinted	Safety Yellow	Yes	100 PC	12.8 lbs.	069165846496
OF-VS3-03	Clear	Blue	Yes	100 PC	12.8 lbs.	069165846502
OF-VS3-83	Tinted	Blue	Yes	100 PC	12.8 lbs.	069165846519
OF-VS3-09	Clear	Pink	Yes	100 PC	12.8 lbs.	069165846526
OF-VS3-89	Tinted	Pink	Yes	100 PC	12.8 lbs.	069165846533