


# RECLAIM® ACRYLIC SNEEZE GUARD – Freestanding Tabletop/Desk Mount

## Product Specifications

Item Number	DIVTT
Panel Material	Clear acrylic (24" and 30" tall models) or frosted acrylic (30" tall models)
Panel Thickness	1/4"
Gap Between Desktop and Panel	1/2"
Foot Material	Powder-coated aluminum and steel
Required Tools for Assembly	Allen wrench (included)
Includes	1 panel and 2 or 3 feet (see chart on page 2)
Weights and Dimensions	See chart on page 2
Cleaning	Clean with a microfiber cloth and a solution of mild dish soap and water or commercial plastic cleaners rated safe for use on acrylics.*
Marker Compatibility	Water-soluble dry-erase markers only**
Warranty	5 year limited warranty




DIVTT-6024C-3024 shown



Frosted acrylic panel also available




DIVTT-CLAMP




DIVTT-2424C




DIVTT-3024C




DIVTT-4824C




DIVTT-6024C




DIVTT-2430C



DIVTT-3030C



DIVTT-4830C



DIVTT-6030C

To Order, Call Your Sales Representative or 800-323-4656

## DIVTT – SPEC SHEET

Product #	Product Description	Height	Width	Panel Color	# of Clamps	Shipping Method	Box Length	Box Width	Box Height	Shipping Weight	Panel Weight
DIVTT-2430F	24" x 30" Frosted Acrylic Divider w/ 2 Tabletop Feet	30"	24"	Frosted	2	Ground	33"	26"	1"	12 lbs.	6.1 lbs.
DIVTT-3030F	30" x 30" Frosted Acrylic Divider w/ 2 Tabletop Feet		30"				33"	32"	1"	14 lbs.	7.7 lbs.
DIVTT-4830F	48" x 30" Frosted Acrylic Divider w/ 2 Tabletop Feet		48"				52"	32"	1"	21 lbs.	12.2 lbs.
DIVTT-6030F	60" x 30" Frosted Acrylic Divider w/ 3 Tabletop Feet		60"		64"		32"	1"	27 lbs.	15.3 lbs.	
DIVTT-2430C	24" x 30" Clear Acrylic Divider w/ 2 Tabletop Feet	30"	24"	Clear	2		33"	26"	1"	12 lbs.	6.1 lbs.
DIVTT-3030C	30" x 30" Clear Acrylic Divider w/ 2 Tabletop Feet		30"				33"	32"	1"	14 lbs.	7.7 lbs.
DIVTT-4830C	48" x 30" Clear Acrylic Divider w/ 2 Tabletop Feet		48"				52"	32"	1"	21 lbs.	12.2 lbs.
DIVTT-6030C	60" x 30" Clear Acrylic Divider w/ 3 Tabletop Feet		60"		64"		32"	1"	27 lbs.	15.3 lbs.	
DIVTT-2424C	24" x 24" Clear Acrylic Divider w/ 2 Tabletop Feet	24"	24"	Clear	2		28"	26"	1"	10 lbs.	4.9 lbs.
DIVTT-3024C	30" x 24" Clear Acrylic Divider w/ 2 Tabletop Feet		30"				33"	26"	1"	12 lbs.	6.1 lbs.
DIVTT-4824C	48" x 24" Clear Acrylic Divider w/ 2 Tabletop Feet		48"				52"	26"	1"	18 lbs.	9.8 lbs.
DIVTT-6024C	60" x 24" Clear Acrylic Divider w/ 3 Tabletop Feet		60"		64"		26"	1"	22 lbs.	12.2 lbs.	

**IMPORTANT WARNINGS:**

**\*Proper Care and Cleaning of Acrylic – PLEASE READ BEFORE INSTALLING:** Acrylic sheeting can be damaged by harsh solvents and cleaners. Only use cleaning products labeled "commercial plastic cleaners", or mild soap and water to remove dirt and debris. When applying the cleaner, use a non-abrasive lint-free or microfiber cloth that won't scratch the surface. Never use products containing ammonia, acetone, carbon tetrachloride, scouring compounds, alcohol, bleach, aromatics, or gasoline. Chemical glass cleaners (even if they are environmentally friendly, organic, or non-scented) are also not to be used. All solvents need to be wiped clean with fresh water and blotted dry to reduce and prevent water spotting. Failure to adhere to the above guidelines can cause yellowing, cracks, and scratches in acrylic sheeting and may give the surface a frosted appearance. It will also void the Limited Warranty – our Limited Warranty does not apply to any damage caused by or the result of improper cleaning, handling, installation, operation, maintenance, pressure washing, accident, fire, natural disaster, explosion, abuse, vandalism, chlorine, chemicals from sprinkler systems, or other external forces. This warranty shall be null and void if any harmful solvents are used to clean.

**\*\*Use of Dry-Erase Markers:** Water-soluble dry-erase markers are safe for use on these acrylic panels. Other forms of dry-erase markers are not recommended because they will be difficult to erase and could possibly leave stains and ghosting.