

# Drill Sets

## 1/2" Reduced Shank S & D Drill Sets, 118° Point



Drills

1/2" Reduced Shank S & D Drill Sets						
No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>1000N Series 1/2" Shank S &amp; D Drill Sets</b>						
5	Nitro®	High Speed Steel	Black & Gold	118°	9/16" - 1" BY 8ths	1000N5
8	Nitro®	High Speed Steel	Black & Gold	118°	9/16" - 1" BY 16ths	1000N8
32	Nitro®	High Speed Steel	Black & Gold	118°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000N32
<b>1000 Series 1/2" Shank S &amp; D Drill Sets</b>						
5	USA	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 8ths	1000A5
8	USA	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 16ths	1000A8
32	USA	High Speed Steel	Bright & Black	118°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000A32
<b>1000C Series 1/2" Shank S &amp; D Drill Sets</b>						
5	USA	Cobalt	Black & Gold	118°	9/16" - 1" BY 8ths	1000C5
8	USA	Cobalt	Black & Gold	118°	9/16" - 1" BY 16ths	1000C8
32	USA	Cobalt	Black & Gold	118°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000C32
<b>1000F Series 1/2" Shank S &amp; D Drill Set</b>						
5	USA	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 8ths	1000F5
8	USA	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 16ths	1000F8
32	USA	High Speed Steel	Bright & Black	118°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000F32

## 1/2" Reduced Shank S & D Drill Sets & Reduced Shank Drill Sets



1000A8



1000N32

### 1/2" & 3/8" Reduced Shank S & D / Reduced Shank Drill Sets

No. of Pieces	Brand	Material	Coating/Finish	Point Angle	Description	EDP No.
<b>1000EC Series 1/2" Shank S &amp; D Drill Sets</b>						
5	–	Cobalt	Bronze	135°	9/16" - 1" BY 8ths	1000EC5
8	–	Cobalt	Bronze	135°	9/16" - 1" BY 16ths	1000EC8
32	–	Cobalt	Bronze	135°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000CE32
<b>1000EF Series 1/2" Shank S &amp; D Drill Sets</b>						
5	–	High Speed Steel	Black & Gold	135°	9/16" - 1" BY 8ths	1000EF5
8	–	High Speed Steel	Black & Gold	135°	9/16" - 1" BY 16ths	1000EF8
32	–	High Speed Steel	Black & Gold	135°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000EF32
<b>1000E Series 1/2" Shank S &amp; D Drill Sets</b>						
5	–	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 8ths	1000E5
8	–	High Speed Steel	Bright & Black	118°	9/16" - 1" BY 16ths	1000E8
32	–	High Speed Steel	Bright & Black	118°	STAND 1/2" - 1" BY 64ths W/DRILLS	1000E32
<b>1035N &amp; 1045N Series 3/8" Reduced Shank Drill Sets</b>						
15	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 32nds	1035N15
29	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 64ths	1035N29
15	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 32nds	1045N15
29	Nitro®	High Speed Steel	Black & Gold	135°	1/16" - 1/2" BY 64ths	1045N29