

# SLIMdri™ Hand Dryer



Surface-Mounted ADA Compliant Hand Dryer



**WORLD DRYER**



- Fast dry time
- Energy efficient
- Universal voltage (110 to 240 Volts)
- ON/OFF heat options
- Long term 10 year limited warranty



**IP23**



# SLIMdri™ Hand Dryer

## Surface-Mounted ADA Compliant Hand Dryer

SLIMdri™ is an energy efficient surface-mounted ADA compliant hand dryer. The SLIMdri hand dryer is perfect for all commercial washrooms. The On/Off heating control, stylish low-profile design with flexible cover options and universal voltage features fit any décor or washroom environment.

**Fast** - Up to 40% faster dry time than leading competitive surface-mounted ADA compliant hand dryers

**Energy Efficient** - Up to 70% less energy than competitive dryers

**Universal Voltage** (110-240 Volts) - Adapts to all electrical supplies.

**Hygienic** - SteriTouch® antimicrobial technology inhibiting the growth of bacteria, mold and fungus extending the dryer's service life

**Flexible** - ON/OFF heat options

**Slim Design** - Compact, sleek and modern design complements any washroom décor.

**Easy Installation** - Reduces installation costs

**Automatic Operation** - Promotes healthy hygiene.




### Electrical Specifications

|       | 110-120 V | 208 V | 220-240 V |
|-------|-----------|-------|-----------|
| Amps  | 8.3       | 3.7   | 4.1       |
| Watts | 950       | 775   | 950       |
| Hz    | 60 Hz     | 60 Hz | 60 Hz     |

### Performance

| Air Speed | Air Flow | Temperature Rise |
|-----------|----------|------------------|
| 140 MPH   | 70 CFM   | 48°F             |

## Specifications



Aluminum , White



Aluminum , Polished Chrome



Aluminum , Brushed Chrome



Aluminum , Black



Stainless Steel , Brushed



Stainless Steel , Polished

| Cover Material  | Cover Finish / Kit | 110-120 / 208 / 220-240 V | Unit Weight        | Shipping Weight    | Unit Size (HxWxD) inch/mm            | Shipping Size (HxWxD) inch/mm      |
|-----------------|--------------------|---------------------------|--------------------|--------------------|--------------------------------------|------------------------------------|
| Aluminum        | White              | # L-974                   | 9.0 lbs / 4.1 kgs  | 10.6 lbs / 4.8 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |
| Aluminum        | Polished Chrome    | # L-970                   | 9.0 lbs / 4.1 kgs  | 10.6 lbs / 4.8 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |
| Aluminum        | Brushed Chrome     | # L-971                   | 9.0 lbs / 4.1 kgs  | 10.6 lbs / 4.8 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |
| Aluminum        | Black              | # L-162                   | 9.0 lbs / 4.1 kgs  | 10.6 lbs / 4.8 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |
| Stainless Steel | Polished           | # L-972                   | 10.7 lbs / 4.8 kgs | 12.3 lbs / 5.5 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |
| Stainless Steel | Brushed            | # L-973                   | 10.7 lbs / 4.8 kgs | 12.3 lbs / 5.5 kgs | 10.7" x11.43" x 3.9" 271 x 290 x 100 | 13.8" x 13" x 6.9" 350 x 330 x 175 |



5700 McDermott Drive, Berkeley, IL 60163  
 Tel: (800) 323-0701, (708) 449-6950  
 Fax: (708) 449-6958  
 www.worlddryer.com

92-MT050 Rev07



Distributor