



Oxivir® Tb

General Virucide, Bactericide, Tuberculocide, Fungicide, Sanitizer

A ready-to-use cleaner disinfectant based on proprietary AHP® technology to deliver fast, effective cleaning performance.

- One-step cleaner disinfectant powered by AHP® technology
- Effective against key pathogens – TB, MRSA, Norovirus and VRE
- Kills HBV, HCV and HIV in 1 minute. Tuberculocidal in 5 minutes and Fungicidal in 3 minutes
- No VOCs, no added fragrance and no NPEs. Environmentally responsible – active ingredient breaks down to oxygen and water
- Compatible with most hard, non-porous surfaces and is a 30 second soft-surface sanitizer

Applications

- Clean and disinfect high-touch surfaces in just ONE Minute
- Non-irritating to eyes and skin





Oxivir® Tb

General Virucide, Bactericide, Tuberculocide, Fungicide, Sanitizer

Use Instructions: As a One-Step Cleaner Disinfectant

- Pre-clean heavily soiled areas.
- Apply product by coarse trigger spray to hard, non-porous inanimate surfaces.
- All surfaces must remain visibly wet for 1 minute. Use 5-minute contact time for TB and a 3-minute contact time for fungi.
- Air Dry, wipe surfaces to dry and remove any residue, or rinse with potable water as necessary.

Note: Rinsing is not necessary unless floors are to be coated with finish or restorer. All food contact surfaces must be rinsed with potable water. Do not use on glassware, utensils, or dishes. Prior to first use on a particular surface, it is recommended to test in a small, discreet area if there is concern of incompatibility, or contact a Diversey representative.

To Spot Sanitize Soft Surfaces

- Remove gross filth prior to sanitization.
- Hold bottle upright 6" – 8" from surface.
- Spray until fabric is wet. **DO NOT SATURATE.** Allow surface to remain wet for 30 seconds.
- Gently blot with a clean, damp, color safe cloth and/or let air dry. For difficult odors or heavy fabrics, repeat application.

Technical data	Oxivir® Tb
EPA Reg. No.	70627-56
Color/Form	Colorless, liquid
pH	3
Scent	Natural cherry almond (no fragrance added)
Shelf Life	2 Years

Product	Pack size	Dilution	Product code	
Oxivir® Tb	12 x 32 fl. oz. / 946 mL Flip Top Bottles Plus Two Trigger Sprayers	Ready-to-use	4277285	
Oxivir® Tb	4 x 1 gal. / 3.78 L Containers	Ready-to-use	100898636	
Oxivir® Tb	1 x 330 gal. Tote	Ready-to-use	5871411	
Oxivir® Tb	1 x 55 gal. Drum	Ready-to-use	101104053	
Oxivir® Tb	1 x 5 gal. pail	Ready-to-use	101104055	

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.