



Heavy Duty Prespray

Heavy Duty Prespray cleans heavily soiled carpets with a unique polymer-enhanced formula that also prevents resoiling.

Features & Benefits

- Effectively cleans tough soils in heavy traffic areas
- Carpets stay cleaner longer due to exclusive soil barriers that help resist resoiling
- CRI and WoolSafe approved products

Applications

- For use on heavily soiled wool and synthetic carpets
- Use for advanced generation carpets when directions on label are followed)





Heavy Duty Prespray

Use instructions

For Prespray Cleaning

- Thoroughly vacuum carpet and pre treat spots.
- Dilute 10 oz. Heavy Duty Prespray with 1 gallon hot water (1 L with 12 L) in pump-up sprayer or fill directly from J-Fill® dispenser.
- Spray carpet completely, paying particular attention to traffic lanes and spots.
- Agitate with a carpet rake, extractor brush, shampoo brush or bonnet.
- Allow 5–10 minutes for Heavy Duty Prespray to completely loosen soils.
- Thoroughly extract carpet with Extraction Rinse according to use directions. Use Liquid Defoamer in recovery tank if required.

For Bonnet Cleaning

- Dilute at 1:32 or 4 oz./gal. (35 mL per L) with warm water.
- Apply light mist onto carpet bonnet.
- Bonnet buff carpet with your pad. Flip pad when soiled. When both sides are soiled, rinse or launder.
- This solution can also be used for spot treatment. Treat spot, agitate and rinse thoroughly.

Technical data	SC	Heavy Duty Prespray
Color/Form		Clear yellow, liquid
pH		8.2 (Concentrate) 7.78 (Use Dilution 1:40)
Scent		Floral fruity
Shelf Life		2 years

Technical data	Concentrate	Heavy Duty Prespray
Color/Form		Clear yellow, liquid
pH		8.0 (Concentrate) 7.5 (Use Dilution 1:12)
Scent		Floral fruity
Shelf Life		2 years

Technical data	93515034 RTD	Heavy Duty Prespray Plus
Color/Form		Clear yellow, liquid
pH		8.2
Scent		Floral fruity
Shelf Life		2 years

Product	Pack size	Dilution	Product code	
Heavy Duty Prespray	4 x 1 gallon / 3.78 L Container	1:12, 1:32	904266	
Heavy Duty Prespray	2 x 2.5 L / 84.5 oz. J-Fill® Bottles - SC	1:40	904274	
Heavy Duty Prespray Plus	2 x 1.5 L / 50.7 oz. RTD	1:40, 1:320	93515034	

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate.

WoolSafe Approved® logo is a registered certification mark owned by the WoolSafe Organization.

CRI Seal of Approval Logo is a certification mark owned by the Carpet and Rug Institute.

www.diversey.com

© 2019 Diversey, Inc. All Rights Reserved. PSS248 (19/119)