



BreakDown™/MC

40

Odor Eliminator

BreakDown™/MC contains a non-pathogenic bacteria that counteracts and eliminates the source of odors.

Features & Benefits

- Odor eliminator and cleaner that contains enzyme producing bacteria which counteracts and eliminates the source of odors
- Versatile formula can lighten grout over time giving it a cleaner look
- Available in two fragrances that help to effectively eliminate odors instead of just masking them

Applications

- Can be used in washrooms, on floors, counters, urinals, walls, carpets, shower and locker rooms, and drains to remove odors





Use instructions

- Use BreakDown™/MC Odor Eliminator on all organic odors and stains.
- General Deodorizing: Dilute 1:32 with water (4 ounces per gallon/ 31 mL per liter).
- Washroom: Dilute 1:20 with water (6 ounces per gallon/50 mL per liter). Apply around urinals, toilets, on floors and in trash receptacles.
- Plumbing Pipes (drains, sinks, disposals, toilets): Pour 4 ounces (120 mL) of BreakDown™/MC Odor Eliminator into drain pipes 2 times per week when drain flow is lowest.
- Carpet Odors and Stains for Spotting: Test carpet for colorfastness. Use BreakDown™/MC Odor Eliminator full strength. Follow good spotting procedures. Re-apply BreakDown™/MC Odor Eliminator. Let stand 20 minutes.
- General Carpet Cleaning: Dilute 1:64 with diluted cleaning solution (2 ounces per gallon/15.6 mL per liter).

Technical data	BreakDown™/MC
Certifications	None
Color/Form	Red, liquid
pH	7.0 - RTD (Fresh) 7.0 (Fresh Concentrate and RTU) 7.0 (Fresh XC and Use Dilution 1:10) 7.0 (Cherry Almond XC) 8.0 (Cherry Almond Use Dilution 1:10) 7.5 (Cherry Almond Concentrate and RTU)
Scent	Fresh/Cherry Almond
Shelf Life	2 Years

Product	Pack size	Dilution	Product code	
BreakDown™/MC Fresh	4 x 1 gallon / 3.78 L Containers	Ready-to-use -1:64	94291110	
BreakDown™/MC XC Fresh	2 x 1.5 gal. / 5.68 L Command Center™/MC	1:10, 1:64, 1:128	94377150	
BreakDown™/MC Cherry Almond	4 x 1 gallon / 3.78 L Containers	Ready-to-use -1:64	94355110	
BreakDown™/MC XC Fresh Concentrate	2 x 84.5 oz. / 2.5 L J-Fill®	1:128	95773791	
BreakDown™/MC Fresh Concentrate	2 x 50.7 oz. / 1.5 L RTD®	1:40, 1:28	100979444	
BreakDown™/MC Fresh Concentrate	1 x 1.32 gal. / 5 L RTD®	1:40, 1:28	100984625	
BreakDown™/MC	12 x 32 oz./946 mL Spray Bottles		D1225695	
BreakDown™/MC XC	12 x 32 oz./946 mL Spray Bottles		D1225694	

Safe handling

Please make sure your employees read and understand the product label and Safety Data Sheet before using this product. The label contains directions for use; and both the label and SDS contain hazard warnings, precautionary statements and first aid procedures. SDS are available online at www.diversey.com or by calling 888.352.2249. Improper use or dilution may result in damage to surfaces and may result in health and physical hazards that match those of the concentrate. Please refer to the Diversey HazMat Library, only available through Internet Explorer, <http://naextranet.diversey.com/dot/>, for up-to-date shipping information.