

# JACKSON\*

SAFETY Brand

## JACKSON SAFETY\* Hellraiser\* Safety Glasses

Codes: 20539, 28615, 20541, 20542, 25716, 25714, 20544, 20543, 20545

### Product Information

Code	Former Code	Lens	Frame/Temples	% VLT	Quantity
20539	3013851	Clear	Black	87 - 93	1 each/bag; 12 bags/case
28615	3013853	Clear, Anti-Fog	Black	87 - 93	1 each/bag; 12 bags/case
20541	3013855	Amber	Black	82 - 88	1 each/bag; 12 bags/case
20542	3013857	Light Blue	Black	64 - 70	1 each/bag; 12 bags/case
25716	3013856	Indoor/Outdoor	Black	45 - 55	1 each/bag; 12 bags/case
25714	3013854	Smoke	Black	8.5 - 15	1 each/bag; 12 bags/case
20544	3013859	IRUV Shade 3.0	Black	8.5 - 18	1 each/bag; 12 bags/case
20543	3013858	Blue Mirror	Black	8.5 - 12	1 each/bag; 12 bags/case
20545	3013860	IRUV Shade 5.0	Black	1.18 - 3.16	1 each/bag; 12 bags/case



Property	Description
Standards	<ul style="list-style-type: none"> <li>Meets ANSI Z87.1+2015 standards for high impact</li> </ul>
Protection	<ul style="list-style-type: none"> <li>Impact</li> <li>99.9% UVA/UVB/UVC protection</li> <li>IRUV Shade 3 lenses protect against infrared (IR) and ultraviolet radiation (UVA/UVB) during tasks like light cutting and brazing (20544 only)</li> <li>IRUV Shade 5 lenses protect against infrared (IR) and ultraviolet radiation (UVA/UVB) during tasks like medium cutting and brazing (20545 only)</li> </ul>
Base Curve	8
Features	<ul style="list-style-type: none"> <li>Sunglasses styling with a compact, lightweight design for comfort as stand-alone PPE and when used with other PPE like face shields and welding hoods</li> <li>Flex-point temples for comfort and stability</li> <li>Hardcoated lenses for scratch resistance and longer life</li> <li>Anti-Fog coating to prevent fogging; ideal for humid environments and temperature variances (28615 only)</li> </ul>
Materials	<ul style="list-style-type: none"> <li>Polycarbonate Lenses</li> <li>Nylon Frame and Temples</li> <li>Stainless Steel Screws</li> </ul>
Storage	<ul style="list-style-type: none"> <li>Keep in dry, clean conditions away from direct sunlight and chemical and abrasive substances, and protect against mechanical impacts</li> </ul>
Cleaning/Maintenance	<ul style="list-style-type: none"> <li>Rinse thoroughly with warm water and dry with a soft cloth. For anti-fog coated lenses (28615) use a soft dry cloth only, as liquids can degrade the performance of the anti-fog coating.</li> <li>Replace eyewear immediately if visibility is reduced or becomes damaged</li> </ul>
Warning	<ul style="list-style-type: none"> <li>Do not operate a vehicle while wearing IRUV lenses.</li> </ul>

For additional information: 1-800-255-6401 or [KCPIInfo@kcc.com](mailto:KCPIInfo@kcc.com)

Kimberly-Clark warrants that its products (1) comply with K-C's standard specifications as of the delivery date to K-C's authorized distributors/direct purchasers and are warranted for the following periods from end user's date of purchase (verified by valid sales receipt) (a) five years for Balder Technology auto darkening filters; (b) two years for all other auto darkening filters; and (c) one year for powered air purifying respirators; (2) comply with all K-C labeling representations; and (3) are manufactured in compliance with all applicable federal, state, and local laws in effect at the time and place of manufacture of the products. THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. K-C is not liable for any kind of special, incidental, or consequential damages. K-C's liability for breach of contract, tort or other cause of action shall not exceed the product purchase price. Purchasers and users are deemed to have accepted the above warranty and limitation of liability, and cannot change the terms by verbal agreement or by any writing not signed by K-C. To the extent required by applicable law, K-C does not limit its liability for death/injury resulting from K-C's negligence.

