

Aerosols



Coil Cleaners

Blackhawk®

An expanding foam coil cleaner. Formulated to deeply penetrate the coil, it liquefies to quickly remove grease, grime, or oily soils from deep within the coil. Blackhawk's formulation is safe and problem-free for cleaning evaporator or condenser coils in an occupied building; produces no objectional fumes. It is particularly effective on coils on refrigerators, coolers, and freezers located in restaurants and other commercial establishments. NSF registered.

18 ounce can 4127-75



Cal-Blast®

A "no-rinse required," coil cleaner with a powerful and effective blasting spray. Cal-Blast dissolves stubborn, resistive deposits and oils that are found to plug coils, particularly those found in kitchen applications, and has a high dielectric strength and non-flammable formula that will not short out electrical equipment. Quick-drying solvent that leaves no residue and has a pleasant citrus scent.

20 ounce can 4132-20



Evap-Fresh® No Rinse Evaporator Coil Cleaner & Disinfectant

A ready-to-use, no rinse evaporator coil cleaner and disinfectant that effectively cleans as well as kills mold, slime and bacteria. This one step disinfectant cleaner is perfect for air conditioners, commercial air handling units, HVAC cooling coils, refrigeration equipment and evaporator coils.

18 ounce can 4166-75



Evap Foam® No Rinse

A "no rinse", high performance, heavy duty detergent, specifically formulated with special surfactants and alkaline cleaners that have been developed into a foaming, no-rinse product. The aerosol product can be sprayed either right side up or upside down, and is ideal for use on most coils, but particularly suited for cooling or evaporator coils.

18 ounce can 4171-75



Coil Cleaners

Nu-Blast® Condenser Coil Cleaner

A "no-rinse formula" condenser coil cleaner in a convenient aerosol package. Double action of high pressure blast and solvent cleaning restores efficiency of condenser coils, quickly and easily. Perfect for removing grease & oil on condenser coils. Nu-Blast formula is non-conductive, non-flammable and is great to use when rinsing is not an option.

18 ounce can 4290-75



Nu-Brite®

A very effective degreaser and cleaner on condenser coils. It's high foaming characteristic will help push soil deposits out of the coil and leave a clean and bright coil. It can also be used as a kitchen degreaser by emulsifying stubborn, resistive grease deposits found on coils located in kitchens. Product should be used where adequate rinsing is available.

18 ounce can 4291-18



Tri-Pow'r HD

Tri-Pow'r HD aerosol provides a powerful foaming spray to assist in lifting debris off of coils. It's a detergent, degreaser and deodorizer – all in one convenient spray. Suitable for any coil design, including microchannel. Tri-Pow'r HD can be used for evaporator "no-rinse" applications where ample condensate will self-rinse the coil.

19 ounce can 4371-75

Adhesive Products

Spray Adhesive

A fast-drying, all-purpose product that provides a strong, water-resistant, flexible bond. It is translucent and does not penetrate or soak material causing bleed-through. Spray Adhesive is excellent for labeling, bonding, splicing and sealing paper, cardboard, cloth, rubber, Styrofoam, canvas, leather, wood, and most plastics.

11 ounce can 4080-04



Spray-n-Bond™

A wide web spray adhesive formulated specifically for insulation and duct liner applications. It is ideal for porous surfaces. It is waterproof, flexible, transparent and non-staining, and it can be used for both temporary or permanent bonds. Formulated with the environment in mind, and contains no chlorinated solvents or ozone depleters.

12 ounce can 4369-75

12 ounce can 4369-85 (Low VOC)



Industrial Products

Electrical Contact Cleaner

Electrical Contact Cleaner cleans, lubricates, and protects electrical contacts from corrosion, and is safe on most plastics. Cleaning action quickly removes greases, dust, and oxidation, restores and maintains precision and efficiency to the instrument and component. Includes extension tube for pinpointing application. USDA Approved.

11 ounce can 4082-03

14 ounce can 4082-04 (Low VOC)



Degreasing Solvent ef

An "environmentally friendly" degreasing solvent, specially formulated for cleaning and degreasing equipment where washing or flushing is not possible. Simply spray it on and wipe it off. Penetrates quick and deep, loosening and liquefying heavy greases and tar. It is noncorrosive, nonstaining, and has a dielectric strength over 26,000 volts.

14 ounce can 4083-75

14 ounce can 4083-83 (Low VOC)



Specialty Products



Zinc Rich Cold Galvanizing

Highly resistant to nearly all forms of corrosion. Perfect for repairing factory galvanized material damaged in shipment, welding, assembly, etc. It's 95% pure zinc film fuses itself to iron, steel or aluminum. Blends well with hot-dip coating. Meets or exceeds Military Specifications MIL-P- 26915A, MIL-T- 26433, MIL-P- 21035, MIL-P-46105 and the Preece Test.

13 ounce can 4087-03

Nu-Kill® Max Strike

A "quick-kill" spray formulation EPA registered to instantly and effectively kill wasps, hornets, yellow jackets, and scorpions from distances up to 20 feet. Nu-Kill II also kills with residual action as wasps and hornets return to a treated nest. The formula is safe in and around electrical equipment, having a dielectric strength of 57,200 volts.

13.5 ounce can 4292-75



Pan-Spray®

A quick and easy to use water proof rubberized coating that won't chip, flake, or peel. It's ideal for sealing out rust and corrosion as well as leaky condensate pans, cooling towers, swamp cooler, roofing, gutters and down spout. Pan Spray is the perfect solution for emergency and permanent repair. Dries in about 30 minutes and one can will cover 20 square feet.

16 ounce can 4296-50 White 4296-51 Black

Pipe-Dri®

Aerosol insulation which provides a moisture barrier to stop sweating and dripping on refrigeration lines, air conditioning lines and other cold surfaces. Quickly adheres and dries to a hard water proof coating. Pipe-Dri makes it possible to insulate hard to reach areas.

18 ounce can 4297-75



Pump Protector

Protects seasonally operated pumps against corrosion during shutdowns by "winterizing" them. When corrosion occurs in close-tolerance areas, it can cause the impeller to stick or bind. Protect your client's investment and your reputation! Safe for all types of water pumps and it requires no special rinsing at start-up.

10 ounce can 4299-T8

A/C Shine®

A specially formulated to clean and protect the painted metal surfaces of outdoor A/C condensing units. It sprays on and wipes off quickly and easily without water. For use on all outdoor unit painted surfaces.

12 ounce can 61118



Specialty Products

CleanVu Glass Cleaner

CleanVu is a highly effective aerosol cleaner for glass and all hard, non-porous surfaces. Its fast-drying, non-filming formula cleans dirt and grime, providing streak-free shine. Ideal for cleaning glass doors on refrigeration cases, CleanVu leaves behind nothing but clear shine and a pleasant lemon scent. Simply spray on glass and wipe off with a soft cloth.

19 ounce can 4081-85



Stainless Steel Cleaner

Nu-Calgon's aerosol Stainless Steel Cleaner removes light soil and restores shine to stainless steel, chrome and hard, washable surfaces. Stainless Steel Cleaner is an oil based cleaner that is ideal for cleaning refrigerated display cases, stainless steel appliances, brushed aluminum, and other shiny metal surfaces. Spray on a small area at a time, and overlap cleaned areas, polishing to perfection!

15 ounce can 4084-75

Lubricants



Food-Grade Silicone

It sprays a perfect non-stick surface on ice machine surfaces, vending machines, coin slots, slicing machines, dairy machinery, and other food processing and packaging equipment. An excellent lubricant that prevents binding and sticking. Contains ingredients approved by the F.D.A. for food contact use. USDA Approved.

11 ounce can 4084-03

V-Belt Dressing

Specially formulated to penetrate and extend modern V-Belt life and designed to maintain efficiency and performance under today's increasing performance requirements. Keeps belts pliable, prevents slippage and does away with squealing and chattering. USDA Approved.

11 ounce can 4086-03



Penetrate HD®

Loosens rusted and frozen metal parts. Frees stuck fan blades, blower shafts, pulleys, rusted nuts and bolts, and any frozen, rusted, or seized metal part. Unique low surface tension formula penetrates into the smallest spaces and breaks and dissolves the bonds of rust and corrosion. Lubricates and protects metals. Dielectric strength 40,000 volts.

12 ounce can 61105 12 ounce can - LV* 61107
17 ounce can 61106 17 ounce can - LV* 61108

Insulation Product

Nu-Foam

An expanding polyurethane prepolymer foam. It is used as a sealant and insulating product used on openings created for refrigeration, air conditioning and heating tubes or pipes, duct joints and other areas where unwanted air penetration might occur. Contains no CFC's nor any HCFC's. USDA Approved.

12 ounce can 4293-04
20 ounce can 4293-75



Read and understand the product's label and Safety Data Sheet ("SDS") for precautionary and first aid information. The SDS is available on the Nu-Calgon website at www.nucalgon.com or is returnable by U.S. Mail upon request.

