



Main

| | |
|---------------------------------|-------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Illuminated push-button |
| Device short name | K |
| Type of operator | Spring return |
| Operator profile | Red flush |
| Operator additional information | Full guard in plastic |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 1.18 in (30 mm) |
| Light source | incandescent |
| Bulb base | BA 9s |
| Light block supply | Via integral transformer |
| [Us] rated supply voltage | 110...120 V AC |
| Contacts type and composition | 1 NO |
| Connections - terminals | Screw clamp terminals |
| Operating position | Any position |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-13 |
| Contact operation | Standard |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|--|
| Product certifications | CE UL listed file E42259 CCN NKCR NEMA CSA LR 25490 class 3211 03 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Ordering and shipping details

| | |
|-----------------------|-------------------------------|
| Category | 21426 - 9001 K (NOT KA,KM,KX) |
| Discount Schedule | CS1 |
| GTIN | 00785901027034 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.5 lb(US) (0.23 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|----------------------|
| Package 1 Height | 6.35 in (16.129 cm) |
| Package 1 width | 2.50 in (6.350 cm) |
| Package 1 Length | 16.13 in (40.968 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|