


Loft CF765



- A. Total Fan Height: **12.8"**
- B. Bottom of Blade to Ceiling: **12.8"**
- C. Width of Canopy: **6.5"**
- D. Width of Housing: **7.5"**
- E. Total Fan Diameter: **60"**

LIGHTING

AMPS	0.6
Lumens	N/A
Watts	N/A
CRI	N/A
CCT (K)	N/A
Dimming Light	N/A
Reverse Switch	Manual

PERFORMANCE

Speed	High	Low	
Airflow	6916	2628	CUBIC FT. PER MIN.
Electricity Use	69	13	WATTS (EXCL. LIGHTS)
Airflow Efficiency	101	201	CUBIC FT. PER MIN. PER WATT
RPM	190	70	REVOLUTIONS PER MIN.

CONTROLS

Included

SW46²
4-Speed
Slide Control



Optional

SR400²
4-Speed
Remote Control



¹ Damp Location Rated for BQ, GRT and WW finishes. BS finish not suitable for Damp Locations.
² Controls are recommended for indoor use only.

AVAILABLE FINISHES

NEW! GRAPHITE
CF765GRT - Weather-Resistant Graphite Blades

BARBEQUE BLACK
CF765BQ - Weather-Resistant Barbeque Black Blades

BRUSHED STEEL¹
CF765BS - Brushed Steel Blades

APPLIANCE WHITE
CF765WW - Weather-Resistant Appliance White Blades



FAN SPECIFICATIONS

Diameter	60"
Motor Lead Lengths	80"
Motor Size (mm)	188 x 15
Product Weight	16.7 LBS
Blade Pitch	Contoured
Downrod Length	6" INCL.
Accepts 2.5" Downrod	Y

SHIPPING SPECIFICATIONS

Carton Weight	19 LBS
Length	28.75"
Width	10.5"
Depth	9.5"

ENERGYGUIDE

<p>Estimated Yearly Energy Cost</p> <h1 style="font-size: 2em; margin: 0;">\$12</h1> <p style="font-size: 0.8em; margin: 0;">Cost Range of Similar Models (19" - 84") • Based on 12 cents per kWh and 6.4 hours use per day • Your cost depends on rates and use • Energy Use: 43 Watts</p>	<p>Airflow</p> <h1 style="font-size: 2em; margin: 0;">4,906</h1> <p style="font-size: 0.8em; margin: 0;">Cubic Feet Per Minute</p> <p style="font-size: 0.7em; margin: 0;">• The higher the airflow, the more air the fan will move • Airflow Efficiency: 115 Cubic Feet Per Minute Per Watt</p>
---	--

All estimates based on typical use, excluding lights ftc.gov/energy

Energy information listed above is a weighted average of High and Low speeds tested with the downrod supplied.



A Division of Luminance Brands

1945 S. Tubeway Ave.
Los Angeles, CA 90040

CUSTOMER SERVICE

Tel: 800.346.1340
Fax: 800.346.1381
Email: Sales@LuminanceBrands.com

For our full line of products, visit LuminanceBrands.com