

# DEWALT<sup>®</sup>

**GUARANTEED TOUGH<sup>®</sup>**

**MADE IN THE** ★★★★★  
**USA**  
**WITH GLOBAL MATERIALS**  
LOOK FOR THIS LOGO ON SPECIALLY  
MARKED DEWALT PACKAGES.

**PERFORM  
PROTECT<sup>™</sup>**

**E-CLUTCH<sup>®</sup>**

**E-CLUTCH<sup>®</sup> SYSTEM**  
Activates in Less Than a Tenth  
of a Second When a Pinch/Stall  
Event is Detected.

**HIGH POWER  
13 AMP MOTOR**  
Powerful 1700 Watt Motor Offers  
Lower Field Case Temperatures  
to Improve Durability\*

**DUST EJECTION SYSTEM<sup>™</sup>**  
Contributes to Long Motor Life

**SLIDE SWITCH**  
Allows Switch to be Locked  
into the On Position.

**5-6" TUCKPOINT/  
CUTTING SHROUD**  
• Adjustable Depth Stop  
• Rotating Door for Inside Corners

**INCLUDES**

- (1) 5" (125 mm) / 6" (150 mm) Tuckpoint Shroud
- (1) 5" (125 mm) Type 27 Guard
- (1) Diamond Wheel

\*As compared to previous 13 Amp  
DEWALT Small Angle Grinder Models

**5" (125 mm) / 6" (150 mm) CUTTING &  
TUCKPOINTING DUST SHROUD TOOL KIT**

**DWE46103**

# SPECIFICATIONS | DWE46103

Amps	13.0 AC Amps
No Load Speed	9,000 rpm
Spindle Thread	5/8"-11 (15.9 mm)
Spindle Lock	Yes
Tool Weight (Tool only)	7.7 lbs (3.5 kg)
Max Wheel Diameter	5"/6"
Hose Port Inner Diameter	35 mm
Hose Port Outer Diameter	42 mm
Tool Free Shroud Change	Yes
Tool Free Accessory Change	Yes

## TOOL WARRANTY

<b>3</b> <b>YEAR</b>	<b>1</b> <b>YEAR</b>	<b>90</b> <b>DAY</b>
<b>LIMITED WARRANTY</b>	<b>FREE SERVICE</b>	<b>MONEY BACK GUARANTEE</b>

## RELATED PRODUCTS



4-1/2" / 5"  
HIGH PERFORMANCE  
SLIDE SWITCH GRINDER



6" (150MM) HIGH  
PERFORMANCE SLIDE  
SWITCH GRINDER

SPECIFICATIONS	DWE43131	DWE43140
Amps	13.0 AC Amps	13.0 AC Amps
Max Watts Out/ Max Horsepower	1,700 W/2.3HP	1,700 W/2.3HP
No Load Speed	11,000 RPM	9,000 RPM
Spindle Thread	5/8"-11	5/8"-11
Switch Type	Slide	Slide
Dust Ejection System	Yes	Yes
Tool-Free Flange System	Yes	Yes
E-Clutch® System/ Overload Protection	Yes	Yes
Tool Length (inches)	13	13
Tool Weight	5.5 lbs.	6.2 lbs.
Power Loss Reset	Yes	Yes
Lanyard Ready™	No	No

Dealer Stamp

# 1-800-4DEWALT

# www.DEWALT.com