

Tools for Building, Construction, Engineering and Design Professionals



Model 4020

Easy-to-use, the Measure Master Pro meets the challenge for fast, accurate solutions in the office or on the jobsite. Carry it in your tool box or briefcase.

Built-in Functions Provide Problem Solving Benefits

- Quickly find solutions to building and dimensional problems
- Enter the numbers just as you would say them
- Reduce expensive errors when estimating dimensions, costs and materials

MEASURE MASTER PRO™

FEET-INCH-FRACTION AND METRIC CALCULATOR

Get professional results every time with this handy and easy-to-use tool for projects involving measurements! Work in and convert between dimensional formats including Feet-Inch-Fractions; Decimal-Foot-Inch-Fractions, Yards, Meters, Centimeters and Millimeters, as well as Areas and Volumes. The Measure Master Pro is ideal for faster, more accurate material estimates. Quickly solve Circumference, Circle Area and Arcs. Use it at home or in the shop for on-the-spot calculations for all your projects — saving you time and money!




Work In and Convert Between Dimensions, including Metric



Linear, Area and Volume Measurements



Find Weight and Weight per Volume



Instant Solutions for Circle Area, Circumference, Arcs and More

Measure Master Pro is the choice for:



- Designers
- Craftsmen



- Tradespersons
- Fabricators



- Woodworkers
- Technicians

Product Specifications

Measure Master Pro 4020

Size: 142.8mm x 76.2mm x 15.9mm (5.6" x 3.0" x 0.6")

Weight: 127.5gm (4.5 oz.) Includes Case and Pocket Reference Guide

Power: Two 3-volt (LR-44/A76) Long-life Batteries

Display: 11 Digits (7 normal, 4 fractions) with Full Annunciators

LCD Dimensions: 15.88mm x 63.5mm (0.625" x 2.5")

Accuracy: 10 Digit Internal Accuracy

Included with Every Measure Master Pro: Protective Hard Slide Cover; Long-life Batteries (Two LR44); English and Spanish Quick Reference Guides and Pocket Reference Guides.

Full One-Year Limited Warranty



Protective Slide Cover
Slips on the front to protect the keys and the LCD or on the back when the calculator is in use.



4840 Hytech Drive
Carson City, NV 89706
1-800-854-8075

Visit our website at:
www.calculated.com

Fast, Accurate Solutions for Building Professionals

Compare Calculator Features:

	CONSTRUCTION MASTER PRO	CONSTRUCTION MASTER PRO Trig	CONSTRUCTION MASTER PRO Desktop	MEASURE MASTER PRO
Dimensional Math and Conversions	4065	4080	44080	4020
Full Metrics (m, cm, mm)	✓	✓	✓	✓
Feet-Inch-Fraction, Inch Fraction, Yards	✓	✓	✓	✓
Decimal Feet (10ths, 100ths), Decimal Inches	✓	✓	✓	✓
Preset Fractions (1/2" through 1/64")	✓	✓	✓	✓
D:M:S, Decimal Degree Entry and Conversions	✓	✓	✓	✓
Right Angle Solutions				
Complete Right Angle/Rafter Calculations	✓	✓	✓	
Pitch Key (Slope and Grade)	●	●	●	
Rise, Run, Diagonal/Common Rafters	✓	✓	✓	
Hip/Valley Key	✓	✓	✓	
Jack Rafters Key	✓	✓	✓	
Irregular Hip/Valley and Jacks	✓	✓	✓	
Rafter Cutting angles (Plumb, Cheek and Level Cuts)	✓	✓	✓	
Stair Layout Key	✓	✓	✓	
Stair (Advanced – Riser Limit, Stairwell Opening, Headroom, Floor Thickness)	●	●	●	
Diagonal Key	✓	✓	✓	
Expanded Rake-Wall	✓	✓	✓	
Arched Rake-Wall	●	●	●	●
Studs: Find number On-center	●	●	●	
Area and Volume Solutions				
Square and Cubic	✓	✓	✓	✓
Roof – Bundles, Squares, 4x8 Sheets, Pitch, Plan Area	●	●	●	
Drywall, Siding and Paneling 4x8, 4x9 and 4x12	●		●	
Column/Cone Area and Volume	✓	✓	✓	
Basic Circular Calculations	✓	✓	✓	✓
Advanced Circular Calculations	✓	✓	✓	✓
Weight per Volume Conversions	✓	✓	✓	✓
Length, Width and Height Keys	●		●	●
Block, Footings	✓		✓	
Special Functions				
Trigonometric Function Keys (Sine, Cosine, Tangent, Arcsine, Arccosine, Arctangent)		✓	✓	
Board Feet	✓	✓	✓	✓
Works as a Regular Calculator (+, -, ×, ÷, +/-, %, π, 1/x, x ² , √)	✓	✓	✓	✓
User-Definable Preferences	✓	✓	✓	✓
Entry Editing Backspace Key	✓	✓	✓	✓
Cost per Unit (Total costs based on unit price)	✓	✓	✓	✓
Equal sided Polygon	●	●	●	
Compound Miters	●	●	●	
Crown Angle	●	●	●	
Additional Capabilities and Characteristics				
Paperless Tape	✓	✓	✓	✓
Number of Memories	● 4	● 4	4	4

● = New or Enhanced Features/Functions

MEASURE MASTER PRO™

FEET-INCH-FRACTION AND METRIC CALCULATOR

DESIGNERS • TRADESPERSONS • WOODWORKERS
CRAFTSMEN • FABRICATORS • TECHNICIANS

Dedicated Keys and Functions Make It Easy To Use

Length, Width, Height — Area, Volume, Square-up, Perimeter, Wall Area, Room Area

m, cm, mm — Work in Metric Dimensions

Yds, Feet, Inch, / — Work in Yards, Feet, Inches, Fractions

Conv — Convert to all secondary functions and features

Stor/Prefs — Store and set preferences for Fractions, On-center, Area, Volume, Metric, Degrees

Circ — Advanced Circular Calculations including Area, Circumference, Diameter

Arc — Arc°, Chord, Segment and Pi, Area, Rise, On-center

BdFt — Find total Board Feet

Backspace Key — Easily change entries

= — Paperless Tape