



Model XSC04Z Parts List

A = Standard Equipment

O = Circuit Diagram

Item#	Part#	Description	Q'ty Unit
001	265995-6	TAPPING SCREW 4X18	6 PC.
002	183K24-8	HANDLE SET	1 PC.
	C10 263005-3	RUBBER PIN 6	2 PC.
	C20 817Y03-5	CAUTION LABEL	1 PC.
	D10	INC. 14	
003	854S63-0	XSC04 NAME PLATE	1 PC.
004	231433-0	COMPRESSION SPRING 4	1 PC.
005	419704-7	LOCK OFF BUTTON	1 PC.
006	651083-9	SWITCH C3XA-1PSPM	1 PC.
007	458594-3	SWITCH LEVER	1 PC.
008	231433-0	COMPRESSION SPRING 4	1 PC.
009	632M68-2	SWITCH UNIT	1 PC.
010	620936-3	LED CIRCUIT	1 PC.
011	643874-2	TERMINAL	1 PC.
012	854S71-1	XSC04 SERIAL NO. LABEL	1 PC.
013	265995-6	TAPPING SCREW 4X18	2 PC.
014	183K24-8	HANDLE SET	1 PC.
	C10 263005-3	RUBBER PIN 6	2 PC.
	C20 817Y03-5	CAUTION LABEL	1 PC.
	D10	INC. 2	
015	911253-5	PAN HEAD SCREW M5X30	3 PC.
016	458656-7	MOTOR HOUSING	1 PC.
017	144251-6	INDICATION PLATE COMPLETE	1 PC.
018	458657-5	MOTOR HOUSING COVER	1 PC.
019	265995-6	TAPPING SCREW 4X18	1 PC.
020	620938-9	CONTROLLER	1 PC.
021	629368-1	STATOR	1 PC.
022	458658-3	BAFFLE PLATE	1 PC.
023	265995-6	TAPPING SCREW 4X18	2 PC.
024	519530-5	ROTOR ASS'Y	1 PC.
	D10	25,26 ㄗ#	
025	210022-4	BALL BEARING 626DDW	1 PC.
026	210069-8	BALL BEARING 6900DDW	1 PC.
027	286039-9	CAP	1 PC.
028	346885-3	SHAFT LOCK	1 PC.
029	233117-6	COMPRESSION SPRING 6	1 PC.
030	265995-6	TAPPING SCREW 4X18	2 PC.
031	140D79-4	GEAR HOUSING COMPLETE	1 PC.
	C10 213961-7	O RING 22	1 PC.
032	424715-9	GASKET	1 PC.
033	458661-4	BLADE CASE	1 PC.
034	266737-1	FLAT HEAD SQ. NECK BOLT M6X20	1 PC.
035	262511-5	RUBBER SLEEVE 6	1 PC.
036	265115-2	+ PAN HEAD SCREW M5	1 PC.
037	210065-6	BALL BEARING 625ZZ	1 PC.
038	227809-7	HERICAL GEAR 30	1 PC.
039	227807-1	HERICAL GEAR 17	1 PC.
040	210033-9	BALL BEARING 696ZZ	1 PC.
041	961005-4	RETAINING RING S-9	1 PC.

042	227808-9	HERICAL GEAR 24	1 PC.
043	257728-3	SLEEVE 10	1 PC.
044	285847-5	BEARING RETAINER 14-23	1 PC.
045	210069-8	BALL BEARING 6900DDW	1 PC.
046	143228-8	BEARING BOX COMPLETE	1 PC.
C10	263002-9	RUBBER PIN 4	1 PC.
047	911128-8	P.H.SCREW M4X16 WITH WR	3 PC.
048	326540-3	SPINDLE	1 PC.
049	231792-2	TENSION SPRING 3	1 PC.
050	345470-9	THICKNESS RING	1 PC.
051	345739-1	SPACER	1 PC.
052	140C92-6	SAFETY COVER COMPLETE	1 PC.
053	345739-1	SPACER	1 PC.
054	257938-2	RETAINING RING(EXT) WR-26	1 PC.
055	267802-9	CUP WASHER 13	1 PC.
056	224408-6	INNER FLANGE 30	1 PC.
057	224404-4	OUTER FLANGE 30	1 PC.
058	266925-0	HEX.SOCKET HEX.BOLT M6X18	1 PC.
059	286036-5	CAP	1 PC.
060	347418-7	LEVER PLATE	1 PC.
061	257982-9	BOW STOP RING E-8	1 PC.
062	252265-2	HEX. NUT M6	1
064	941151-9	FLAT WASHER 6	1 PC.
065	251896-4	SCREW M5X20	1 PC.
066	252103-8	HEX. LOCK NUT M5-8	1 PC.
067	162468-9	BASE	1 PC.
068	265056-2	+ PAN HEAD SCREW M5	1 PC.
069	265676-2	H.S.H.B M6X29	1 PC.
070	233267-7	COMPRESSION SPRING 7	1 PC.
071	458652-5	DUST CAP	1 PC.
072	213005-3	O RING 5	1 PC.
073	265995-6	TAPPING SCREW 4X18	3 PC.
074	458659-1	DUST BOX L	1 PC.
075	458660-6	DUST BOX R	1 PC.
076	347417-9	PLATE	1 PC.
077	127011-1	DUST BOX ASSEMBLY	1 PC.
D10		INC. 69-76	
A01	192219-6	SAFETY GOGGLE	1 PC.
A02	783203-8	HEX. WRENCH 5	1 PC.
A03	A-96095	T.C.T SAW BLADE 150X15.88X32T	1 PC.
A04	164095-8	GUIDE RULE	1 PC.