

Construction Calculators
Compare the Features

	Construction Master Pro Model 4065	Construction Master Pro Trig Model 4080	Construction Master 5 Model 4050	Measure Master Pro Model 4020
Work in and convert between all dimensional units				
Feet-Inch-Fraction, Inch Fraction, Yards	✕	✕	✕	✕
Decimal Feet (10ths, 100ths), Decimal Inches	✕	✕	✕	✕
Handles All Construction Fractions	✕	✕	✕	✕
Full Metrics (m, cm, mm)	✕	✕	✕	✕
Weight per Volume Conversions	✕	✕	✕	✕
Right Angle Solutions				
Complete Right Angle/Rafter Calculations	✕	✕	✕	
Pitch Key (Slope and Grade)	✕	✕	✕	
Rise, Run, Diagonal/Common Rafters	✕	✕	✕	
Hip/Valley and Jack Rafters	✕	✕	✕	
Irregular Hip/Valley and Jacks	✕	✕	✕	
Rafter Cutting Angles (Plumb, Cheek and Level Cuts)	✕	✕		
Stair Layouts (Basic and Advanced - Riser Limit, Stairwell Opening, Headroom, Floor Thickness)	✕	✕	Basic	
Rake-Walls	✕	✕	✕	
Studs: Find Number On-center	✕	✕	✕	
Area and Volume Solutions				
Square and Cubic Dimensions	✕	✕	✕	✕
Roof – Bundles, Squares, 4x8 Sheets, Pitch, Plan Area	✕	✕		
Drywall, Siding and Paneling - 4x8, 4x9 and 4x12	✕			
Column/Cone Area and Volume	✕	✕		
Basic and Advanced Circular Calculations	✕	✕	Basic	Basic
Length, Width and Height Keys, Automatic Area and Volume	✕			✕
Blocks, Footings	✕			
Special Functions				
Trigonometric (Sine, Cosine, Tangent, Arcsine, Arccosine, Arctangent)		✕		
Board Feet	✕	✕	✕	✕
Works as a Regular Calculator (+, -, ×, ÷, +/-, %, π, 1/x, x ² , √ ^x)	✕	✕	✕	✕
User-Definable Preferences	✕	✕	✕	✕
Entry Editing Backspace Key	✕	✕	✕	✕
Cost per Unit (Total costs based on unit price)	✕	✕	✕	✕
Equal sided Polygon	✕	✕		
Compound Miters and Spring (Crown) Angle Cuts	✕	✕		
Additional Capabilities and Characteristics				
Paperless Tape	✕	✕	✕	✕
Number of Memories	4	4	1	4
Included with Calculator				
Online User's Guide	✕	✕		
Pocket Reference Guides in English and Spanish	✕	✕	✕	✕
Long-Life Batteries	✕	✕	✕	✕
Full One-Year Limited Warranty	✕	✕	✕	✕