



Infinitely Adjustable Cable Lockout



PRODUCT FEATURES:

- Tough, flexible 6 ft. cable is perfect for any lockout tagout application
- Patented 5/32 in. diameter multi-strand steel cable is insulated with clear plastic coating (PVC free)
- Durable, lightweight thermoplastic body withstands chemicals and extreme environments
- High-visibility, reusable, write-on safety labels (includes English, French & Spanish)
- 4 lock holes to accommodate employee padlocks
- Integrated safety hasp with cable cinching function; cinches tight to remove slack and hold firm remove slack and holds firm
- Available in custom lengths from 2 ft. to 50 ft. long (refer to backside for more information)

Product Number	S806
Description	Cable Lockout, Red Color Finish
Body Material	PBT and PC Thermoplastic (PVC Free)
Cable Material	Multi-Strand steel cable w/ clear plastic coating
Cable Length	Available 2 ft. (.06m) to 50 ft. (15m) custom lengths
Cable Diameter	5/32 in. Diameter
# Lock Holes	4
UPC - Individual	071649147715
Master Carton Quantity	6
UPC - Master Carton	10071649147712



S806 with Butterfly Valve secured with 410RED

Additional Cable Sizes Available

The Master Lock S806 includes a 6 ft. cable. The cable is available in 1 ft. increments from 2 ft. to 50 ft. To order the adjustable cable lockout with specified cable length, add "CBLn" to the end of the product number (ie. S806CBL3 has a 3 ft. cable).

SEE HOW IT WORKS!

Scan this QR code



Additional Products

410 Thermoplastic Padlocks

- Designed exclusively for Lockout/Tagout applications
- Durable, lightweight, non-conductive thermoplastic body
- 6-Pin, reserved for safety cylinder
- Key retaining, ensures padlock is not accidentally left unlocked
- English, Spanish, French Labels included
- Available in 8 vibrant colors



S3920 Butterfly Valve Lockout Device

- Intuitive design locks out valve in seconds by feeding S806 cable lockout through desired eyelet and around valve neck.
- Durable, lightweight thermoplastic resists chemicals & performs effectively in extreme environments
- Adjustable design fits virtually all butterfly valves
- Stainless steel rivet allows device to smoothly pivot open and closed to ensure proper fit



A1100 Anodized Aluminum Padlocks

- Solid body construction stands up to physical abuse
- Excellent corrosion resistance
- Uses FDA approved lubricants safe for use in food processing
- Available with 1 in., 1-1/2 in. or 3 in. tall shackle
- Available in 9 colors for easy identification

