

DEWALT

**PERFORM
PROTECT**

DUST

E-CLUTCH

**13 AMPS,
1700 MAX WATTS OUT,
AND 11000 RPM**

PLUNGING SYSTEM

Designed to improve dust collection when starting and finishing the cut

DUST EJECTION SYSTEM

Ejects damaging dust and debris particles that enter through the air intake vents

AIRLOCK™ READY

Compatible with any dust extractor fitted with a DEWALT AirLock™ connector

DWV9000 Quick Connector



For quick, easy, and durable connection between 1 1/4" vacuum hoses and various tools and shrouds.

**DEPTH OF CUT
ADJUSTMENT LEVER**

Allows for easy depth of cut adjustment up to 1-1/8"

4-1/2" - 5" GRINDER & CUTTING DUST SHROUD KIT

DWE46123

DWE46123 KIT INCLUDES

DWE43131 GRINDER, DWE46125 SHROUD, 5" TYPE 27 GUARD, SIDE HANDLE, HEX KEY, INNER AND OUTER FLANGE, DWV9000 QUICK CONNECTOR, KIT BAG

TOOL WARRANTY

3

YEAR

LIMITED
WARRANTY

1

YEAR

FREE
SERVICE

90

DAY

MONEY BACK
GUARANTEE

DWE46125 - 5" CUTTING DUST SHROUD

Hose Port OD & ID	1.66" AND 1.51"
Max. Wheel Diameter	5"
Depth of Cut	1-1/8"
Weight	2.2 LBS



DWE46127 - 7" CUTTING DUST SHROUD

Hose Port OD & ID	1.66" AND 1.51"
Max. Wheel Diameter	7"
Depth of Cut	1-1/2"
Weight	3.85 LBS



RELATED PRODUCTS



DWE46100

5" - 6" CUTTING & TUCKPOINTING
DUST SHROUD



DWE46103

6" HIGH PERFORMANCE GRINDER & CUTTING/
TUCKPOINTING DUST SHROUD KIT



DWE46152

5" SURFACE GRINDING DUST SHROUD



DWE46153

5" GRINDER & SURFACE GRINDING
DUST SHROUD KIT

www.DEWALT.com 1-800-4-DEWALT

Copyright ©2020 DEWALT. The following are examples of trademarks for one or more DEWALT power tools, accessories, anchors, and concrete adhesives: the yellow and black color scheme; the "D"-shaped air intake grill; the array of pyramids on the handgrip; the kit box configuration; and the array of lozenge-shaped humps on the surface of the tool.