

SO2040M200S

Homeline All In One combination service entrance device, ringed socket, no bypass, OH, 200 A, 10 kA, 20 spaces



Main

Product or component type	All-In-One
Range of product	Homeline
Meter socket type	Ringed
Hub type	A

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Mounting	Surface
Number of spaces	20
Number of circuits	40
Number of Tandem Breakers	20
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...350 kcmil aluminium)line side AWG 6...350 kcmil copper)line side AWG 8...AWG 2/0 aluminium)service ground AWG 8...AWG 2/0 copper)service ground
Tightening torque	Main lugs 250 lb.in, AWG 6...350 kcmil, aluminium/copper Branch lugs 50 lb.in, AWG 14...AWG 1/0, copper Branch lugs 50 lb.in, AWG 12...AWG 1/0, aluminium Branch lugs 50 lb.in, AWG 3...AWG 2/0, aluminium/copper Branch lugs 45 lb.in, AWG 6...AWG 4, aluminium/copper Branch lugs 40 lb.in, AWG 8, aluminium/copper Branch lugs 35 lb.in, AWG 14...AWG 10, aluminium/copper Branch lugs 35 lb.in, AWG 12...AWG 10, aluminium/copper Cover 10 lb.in
Disconnect	Service disconnect (factory installed)
Disconnect Rating	200 A
Branch Breaker Rating	200 A
Service feed location	OH
Bypass type	No bypass
Connections - terminals	Lugs
Width	18.35 in (466.09 mm)
Depth	5.32 in (135.13 mm)
Height	40.93 in (1039.62 mm)

Environment

NEMA Rating	NEMA 3R
Product certifications	UL Listed

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901328032
Nbr. of units in pkg.	1
Package weight(Lbs)	41.93 lb(US) (19.02 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.90 in (14.986 cm)
Package 1 width	14.90 in (37.846 cm)
Package 1 Length	36.40 in (92.456 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------