



Main

Range of product	Altivar
Accessory / separate part category	Connection accessory
Accessory / separate part type	Connecting cable
Product compatibility	TWDNADK70P Modbus splitter block LU9GC3 TSXCUSB485 VW3A8306TF010 VW3A8306TF03
Accessory / separate part destination	Modbus splitter block LU9GC3 Modbus T-junction box Terminal or Modbus network port
Range compatibility	Zelio Logic Altivar 31 Preventa XPS MF Modicon M258 Modicon LMC058 Altistart 48 Altivar 71Q Altivar 32 Altivar 71 Altivar 12 Altivar 61 Altivar Process ATV900 Altivar 212 Altivar Machine ATV340 except Sercos drives Modicon M238 Altivar Easy 610 Altivar 21 Altistart 22 Altivar Process ATV600 Lexium SD3 Altivar 31C Altivar Easy 310 Altivar 61Q Altivar 312 Altivar Machine ATV320
Cable length	0.98 ft (0.3 m)
Electrical connection	2 male connectors - RJ45

Complementary

Net Weight	0.06 lb(US) (0.025 kg)
------------	------------------------

Ordering and shipping details

Category	18062 - MISC. ALTIVAR/ALTISTART CABLES, CONNECTORS
Discount Schedule	CP1G
GTIN	00785901425373
Nbr. of units in pkg.	1
Package weight(Lbs)	0.05 lb(US) (0.02 kg)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.18 in (3 cm)
Package 1 width	2.17 in (5.5 cm)
Package 1 Length	4.33 in (11 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	60
Package 2 Weight	4.52 lb(US) (2.048 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P06
Number of Units in Package 3	480
Package 3 Weight	57.77 lb(US) (26.204 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------