



HONEYWELL UVEX® MILITARY EYEWEAR

One Vision for Countless Challenges.

Uvex Genesis® and Uvex Genesis XC®

Honeywell
UVEX®



A MULTITUDE OF RISKS. ONE EYE SAFETY SOLUTION.

Our soldiers face many challenges in their missions. Our mission, at Honeywell, is to attentively focus on every threat our fighting men and women are exposed to, offering them the high-quality, military tested eye safety solutions they deserve – Honeywell Uvex Military Eyewear.

Honeywell Uvex is an all-in-one solution that provides enhanced protection from dust, flying debris and ballistic hazards both in training and on the battlefield while maintaining compatibility with existing soldier equipment. Honeywell Uvex Military Eyewear is fully compliant to military standards, but it also offers excellent visibility, improved fit, great comfort and style.

Honeywell Uvex has been an acknowledged leader in safety eyewear for more than fifty years. The pioneer of many groundbreaking innovations, Honeywell Uvex is dedicated to protecting military personnel and users throughout all industries, by meeting the highest level of eye safety standards. We focus on protection – you focus on defense.

MILITARY TESTS PASSED – MISSION ACCOMPLISHED.

- Extreme impact (Mil Vo)
- Side protection coverage
- Penetration
- High mass
- Optics
- Transmittance and haze
- Markings check
- Weight and lens thickness
- Chromaticity
- UV
- Abrasion
- Adhesion



UVEX GENESIS® MILITARY EYEWEAR

New Genesis Military meets the new Military Standard. Uvex Genesis for the U.S. Military is the all-in-one solution in protective eyewear. For superior coverage, visibility, comfort, and style, the answer is Uvex Genesis.



EYEWEAR FEATURES

1. Dual 9-base wrap-around polycarbonate lens provides uncompromised peripheral vision and superior ballistic protection
 2. Soft flexible fingers adjust and conform to almost any nasal profile to reduce slippage and improve fit
 3. Soft elastomer brow guard diffuses and deflects impact and provides unparalleled comfort
 4. A unique ventilation channel between the frame and lens, vents the eye socket area to deliver an outstanding level of moisture and fog control
 5. Fixed, styled, temple length with molded, padded temple tips
 6. Three-position ratchet lens inclination adjusts to complete the fitting system and provides unsurpassed extended wear comfort
- Quick, easy and cost-effective lenses can be changed to accommodate different lighting or applications
 - Lightweight frame with streamlined temple design ensures compatibility with helmets, night vision and communication devices
 - Rx lens insert is available for prescription eyeglass wearers
 - Dura-streme® coating minimizes fogging and provides superior scratch resistance
 - Meets U.S. Military MIL-PRF-32432A ballistic impact requirements
 - Certified to the requirements of ANSI Z87.1-2015
 - Lifetime frame guarantee
 - Made in U.S.A. 



Comfort

The soft elastomer of the brow guard provides a comfort pad at all contact points.



Rx Carrier


Stainless steel Rx insert for prescription eyeglass wearers. Rx lenses fit snugly onto the frame, shielding expensive prescription lenses from damage.

LENS TECHNOLOGY

Uvex Dura-streme lens coating delivers the ultimate in anti-fog protection and scratch resistance.

Dura-streme lenses combine our two best lens coatings on one lens: Ultra-dura® on the exterior and Uvextreme® on the interior to provide up to 3x* more lens life. Uvextreme anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura anti-scratch coating is permanently bonded to the lens and is scratch-resistant and chemical-resistant.

**Uvextreme®
Anti-Fog**
on the inside
provides anti-fog
protection near
your hard-
working eyes.



2
**Uvex Dura-streme™
Technology**

**Ultra-dura®
Anti-Scratch**
on the outside adds
up to **3x* more life**
to your lenses by
protecting against
harsh elements.

COMBO PACK

Uvex Genesis Dura-streme Combo Pack**

The Genesis Dura-streme Combo Pack is fit for most non-laser applications and is conveniently packaged in a comprehensive, functional kit. The kit includes:

- Genesis eyewear assembly with black frame and clear Dura-streme anti-fog/anti-scratch lens
- 1 gray sunglass replacement lens with Dura-streme anti-fog/anti-scratch lens
- Uvex Fog Eliminator Plus anti-fog cloth
- Black nylon crush-resistant carrying case, retention strap and storage pouch/cleaning cloth



S99-S3291-MIL5A



* Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application

** MCEPP and APEL approved

UVEX XC[®] MILITARY EYEWEAR

New XC Military meets the new Military Standard. Uvex XC Military Eyewear is a unique solution for unique soldiers. Created to offer the U.S. Army superior ballistic protection, Uvex Genesis XC provides the personnel from our armed forces excellent vision, improved fit and enhanced extended-wear comfort.




EYEWEAR FEATURES

1. Dual 9-base wrap-around polycarbonate lens provides uncompromised peripheral vision and superior ballistic protection
 2. Soft flexible fingers adjust and conform to almost any nasal profile to reduce slippage and improve fit
 3. Soft elastomer brow guard diffuses and deflects impact and provides unparalleled comfort
 4. A unique ventilation channel between the frame and lens, vents the eye socket area to deliver an outstanding level of moisture and fog control
 5. Fixed, styled, temple length with molded, padded temple tips
 6. Three-position ratchet lens inclination adjusts to complete the fitting system and provides unsurpassed extended wear comfort
 7. Wraparound lens for extra cheek and extra side coverage, up to 20% more than the standard Genesis lens
- Rx lens insert is available for prescription eyeglass wearers
 - Meets U.S. Military MIL-PRF-32432A ballistic impact requirements
 - Certified to the requirements of ANSI Z87.1-2015
 - Lightweight frame with streamlined temple design ensures compatibility with helmets, night vision and communication devices
 - Dura-streme[®] coating minimizes fogging and provides superior scratch resistance
 - Quick, easy and cost-effective lenses can be changed to accommodate different lighting or applications
 - Lifetime frame guarantee
 - Made in U.S.A. 

LENS TECHNOLOGY

Uvex Dura-streme lens coating delivers the ultimate in anti-fog protection and scratch resistance.

Dura-streme lenses combine our two best lens coatings on one lens: Ultra-dura® on the exterior and Uvextreme® on the interior to provide up to 3x* more lens life. Uvextreme anti-fog coating performs under the most extreme conditions and will not wear off after repeated cleanings. It is permanently bonded to the lens and retains anti-scratch, anti-static and UV protection properties. Ultra-dura anti-scratch coating is permanently bonded to the lens and is scratch-resistant and chemical-resistant.



COMBO PACK

Uvex XC Dura-streme Combo Pack**

The XC Dura-streme Combo Pack is fit for most non-laser applications and is conveniently packaged in a comprehensive, functional kit. The kit includes:

- XC eyewear assembly with black frame and clear Dura-streme anti-fog/anti-scratch lens
- 1 gray sunglass replacement lens with Dura-streme anti-fog/anti-scratch lens
- Uvex Fog Eliminator Plus anti-fog cloth
- Black nylon crush-resistant carrying case, retention strap and storage pouch/cleaning cloth



S99-S3399-MIL3A



Comfort

The soft elastomer of the brow guard provides a comfort pad at all contact points.



Rx Carrier

Stainless steel Rx insert for prescription eyeglass wearers. Rx lenses fit snugly onto the frame, shielding expensive prescription lenses from damage.

* Comparative lens life test performed using a Bayer Abrasion Test method and may vary between environment and application

** MCEPP and APEL approved

GENESIS ORDERING INFORMATION (MCEPP AND APEL APPROVED)

NSN	PART NUMBER	DESCRIPTION
4240-01-552-4142	S99-S3200D-MIL	Genesis eyewear, black frame, clear Dura-streme® lens
4240-01-551-4148	S99-S3212D-MIL	Genesis eyewear, black frame, gray Dura-streme® lens
4240-01-516-3444	S99-S520-MIL	Black crush-resistant case
4240-01-552-4178	S99-S6900D-MIL	Genesis clear Dura-streme replacement lenses, 10/box
4240-01-552-4181	S99-S6912D-MIL	Genesis gray Dura-streme replacement lenses, 10/box
6540-01-516-5342	S99-S3350-MIL2	Stainless steel Rx carrier, 50pk
4240-01-552-4131	S99-S3291-MIL5A-H5	Genesis Dura-streme® combo kit Includes: Genesis eyewear assembly with clear Dura-streme® lens, gray Dura-streme® sunglass replacement lens, Uvex Fog Eliminator Plus anti-fog cloth, retention strap, storage pouch/cleaning cloth, black crush resistant carrying case
4240-01-641-9430	S479	Uvex Fog Eliminator Plus anti-fog cloth

XC ORDERING INFORMATION (MCEPP AND APEL APPROVED)

NSN	PART NUMBER	DESCRIPTION
4240-01-516-3460	S99-S3300D-MIL	XC eyewear, black frame, clear Dura-streme® lens
4240-01-516-3452	S99-S3301D-MIL	XC eyewear, black frame, gray Dura-streme® lens
4240-01-516-3444	S99-S520-MIL	Black crush-resistant case
4240-01-516-3469	S99-S6950D-MIL	XC clear Dura-streme® replacement lenses, 10/box
4240-01-516-3473	S99-S6951D-MIL	XC gray Dura-streme® replacement lenses, 10/box
6540-01-516-5342	S99-S3350-MIL2	Stainless steel Rx carrier
4240-01-516-5361	S99-S3399-MIL3A	XC Dura-streme combo kit Includes: XC eyewear assembly with clear Dura-streme® lens, gray Dura-streme® sunglass replacement lens, Uvex Fog Eliminator Plus anti-fog cloth, retention strap, storage pouch/cleaning cloth, black crush resistant carrying case
4240-01-641-9430	S479	Uvex Fog Eliminator Plus anti-fog cloth

For More Information

safety.honeywell.com

Technical Service: 800.873.5242

Honeywell Industrial Safety

9680 Old Bailes Road

Fort Mill, SC 29707

US:

Tel. 800.430.5490

Fax. 800.322.1330

Canada:

Tel. 888.212.7233

Fax. 888.667.8477

© 2020 Honeywell International Inc.

