



Now, you can
see clearly

Jackson Safety* Nemesis* Rx Readers Safety Eyewear

Style, comfort, and quality are big drivers of safety eyewear compliance. That's why Nemesis* Safety Eyewear was developed with a sporty style and flexible, lightweight design. With many lens types to choose from, Nemesis* Safety Eyewear offers impact protection for many different work environments.

For workers experiencing far-sightedness, comfort may mean enhancing their ability to see the task at hand without experiencing eyestrain, headaches, or eye fatigue.


Join the millions of people who choose Nemesis* Safety Eyewear day-in-and-day-out for **stylish comfort, lasting protection.**



NEMESIS*
Safety Eyewear

JACKSON*
SAFETY Brand

Jackson Safety* Nemesis* Rx Readers Safety Eyewear



Features

- Meets the ANSI Z87.1+ standards for optical requirements and impact protection, with select codes certified to CSA 94.3-07 by the CSA Group and authorized to bear the CSA Certification Mark
- Polycarbonate lenses provide **99.9% UVA/UVB/UVC protection** to help prevent eye damage like cataracts, retinal damage, and other conditions that can cause temporary vision loss
- Lightweight, wraparound style is designed for **maximum user comfort**, to help users resist the urge to move the glasses to the top of the head, instead of on the face, where they belong
- Choose from a wide selection of lenses to help **reduce eye fatigue** in different environments

Unsurpassed durability is just what you'd expect from a trusted leader recognized for high-quality, reliable eyewear



Number denotes the base curve of the eyewear; a higher base curve provides more wraparound protection and peripheral vision, and can reduce the need for side shields

Nemesis* Rx Readers Safety Eyewear • Pairs/Box: 6



Code	Lens	Strength	Frame	Gravity Feed
28618	Clear	+1.0	Black	●
28621	Clear	+1.5	Black	●
28624	Clear	+2.0	Black	●
28627	Clear	+2.5	Black	●
28630	Clear	+3.0	Black	●
22516 ■	Smoke	+1.5	Black	●
22518 ■	Smoke	+2.0	Black	●
22519 ■	Smoke	+2.5	Black	●

Note: Styles marked with ■ are not CSA Certified



To learn more, please contact your Kimberly-Clark Professional* sales representative or visit www.KCProfessional.com

Contact customer service: 1-888-346-GOKC (4652)

Our Guarantee

Your total satisfaction means everything to us. If, for any reason, our products do not meet your expectations, Kimberly-Clark will reimburse you† for your initial purchase, via FREE product, for up to \$1,000. For more information on Kimberly-Clark Professional*, visit us online at www.KCProfessional.com.

† Guarantee extended to consuming end-user accounts only.