



PIG® High-Reach Roof Leak Diverter Tarp Kit

TLS820 27" x 35" x 12", Leak Diverter Tarp; Hose; Telescoping Pole; Mat Pad; Container, Install With Telescoping Pole

High-ceiling leak in a busy professional area? Funnel the leak safely through this stylish high-reach leak diverter.

- High-reach leak diver quickly routes small emergency roof leaks from high ceilings or in hard-to-reach areas
- Telescoping pole means no need to attach tarp to ceiling; adjustable pole extends to 9 ft.
- One person can easily set up entire leak diverter without a ladder
- Extra-large drain opening with anti-clog debris cage for reliability
- Captures drips from ceilings up to 15-ft. high without splash-out; for even higher ceilings, utilize included absorbent splash pad
- Stylish design looks professional in hotel, airport, hospital, school or elsewhere
- Lid helps prevent your customers or guests from mistakenly dropping items into 5-gallon pail
- Sturdy weight distribution is hard to tip
- High-visibility yellow legs and Caution warning message help pedestrians avoid tripping
- Pole breaks down effortlessly to just over 4 ft.
- Drainage plug and hose cutout make emptying pail convenient; no need to remove lid
- Heavy-duty vinyl-coated tarp resists punctures, UV and mildew to last over repeated uses



Item#	Description	Dimensions	Weight
TLS820-BK		27" W x 35" L x 12" H	12 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
TLS820-BK		69cm W x 89cm L x 30cm H	5.4 kg

Specifications

Dimensions	27" W x 35" L x 12" H
Application	Roofs; Pipes
Brand	PIG

Contains

Leak Diverter Tarp; Hose; Telescoping Pole; Mat Pad;

	Container
Drainage Hose	Included
Flow Rate	3.33 gal./Minute
Hanging Straps	Not Required
Hose Connector	.75"
Installation Method	Telescoping Pole
Shape	Rectangle
Sold as	1 each
Weight	12 lbs.
# per Pallet	12

Composition	Tarp: 10oz. Reinforced PVC Pole: Steel Hose: PVC Bucket: Plastic Splash Pad: Polyester
--------------------	--

Includes	1 - 35"L x 27"W x 12"H Tarp, Black 1 - Adjusts from 4'2" up to 9' Telescoping Pole 1 - 10' L Clear Drainage Hose (TLS690) 1 - 5 Gallon Bucket 5 - ½"W x 12"L Velcro Straps 1 - Black Ring 4 - Metal Rods 1 - Hardware Kit (1 washer, 1 bolt, 1 allen wrench) 1 - 18" W x 22" L Mat Pad
-----------------	--

UNSPSC	24141506
Pigalog® Page Number	Page 250

Metric Equivalent

Weight	5.4 kg
Dimensions	69cm W x 89cm L x 30cm H

Technical Information

Technical Documents

[Instructions for PIG High-Reach Roof Leak Diverter Tarp Kit](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com

