



### Main

Range	Linergy
Product name	HK
Product or component type	Plug outlet
Poles description	3P
[I <sub>th</sub> ] conventional free air thermal current	32 A
I <sup>2</sup> t on activation	200000 A <sup>2</sup> .s
Number of points	2
Number of cables	3 0.01 in <sup>2</sup> (4 mm <sup>2</sup> )
Cable length	0.82 ft (0.25 m)
Quantity per set	Set of 6

### Complementary

[Ui] rated insulation voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak current	25 kA
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.10 lb(US) (0.045 kg)

### Environment

Standards	IEC 60439
Product certifications	DNV LR0S (Lloyds register of shipping) CSA UL

### Ordering and shipping details

Category	22623 - PANEL BUS (AK5)
Discount Schedule	I11
GTIN	00785901576853
Nbr. of units in pkg.	1
Package weight(Lbs)	0.13 lb(US) (0.06 kg)
Returnability	Yes
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.00 in (12.7 cm)
Package 1 width	5.31 in (13.5 cm)
Package 1 Length	6.10 in (15.5 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Weight	14.07 oz (399 g)
Package 2 Height	5.00 in (12.7 cm)

Package 2 width	5.31 in (13.5 cm)
Package 2 Length	6.10 in (15.5 cm)
Unit Type of Package 3	S04
Number of Units in Package 3	96
Package 3 Weight	15.93 lb(US) (7.226 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

### Contractual warranty

Warranty	18 months
----------	-----------