



MUSTEE
Preferred by the "Pros"


80 DURASTALL® Shower Stall 32" x 32"

SEE PAGE 2 FOR A LIST OF ACCESSORIES!



Model 80 shown with optional glass door.

Model 80 Standard Base



Standard bases include a PVC drain for direct connection to a 2" (Sch. 40) ABS, PVC or iron DWV pipe.

Design features:

DURASTALL® Model 80 includes...


- Slip-resistant floor with drain
- Shower valve and head
- Shower curtain and curtain rod
- Safety railing with molded-in soap dish and shampoo holder
- Mold and mildew-resistant components
- Knock-down construction makes portability extremely easy and is free-standing when assembled
- Easy to assemble and install

Optional features:

- Shower door available, sold separately
- Kit to convert standard base into extended base is available, sold separately

Specifications

Model	Color	Size	Base	A	B	C	D	UPC
80	White	32" X 32"	Standard	32-5/8"	75-3/8"	16-5/16"	24"	6 71031 00314 0



General: Furnish and install as shown on plans, free-standing DURASTALL® Shower Stall model ____ (80) as manufactured by E.L. Mustee & Sons, Inc. Consists of three, white, high-gloss thermoplastic walls, molded top frame, rigid aluminum front supports, slip-resistant 32" x 32" base, one-piece wrap-around railing with built-in soap dish and container. Skid-resistant floor with drain assembly, shower valve and head, shower curtain and rod, plus assembly hardware. Placement of valve assembly to be determined by installer.



MUSTEE

E.L. Mustee & Sons, Inc. • 5431 West 164th Street • Brook Park, OH 44142 • Phone: 216.267.3100 • Fax: 216.267.9997
E-mail: info@mustee.com • Web: www.mustee.com • Proudly made in the USA

Notice: Our continuous commitment to product improvement may result in changes to product specifications without notice.
Patents pending. Made and Printed in U.S.A.



MUSTEE

Preferred by the "Pros"

80 DURASTALL® Shower Doors



Design features:

- Fits all DURASTALL® shower stalls
- Sturdy, rust-resistant, engineered aluminum frame with polished chrome finish
- May be hung to open to accommodate a left or right hand opening
- Continuous-pull handle with magnetic seal
- Easy to install and clean...all components are mold and mildew resistant
- Door height is 64"

Glass Door

Model	Type Panel	UPC	Opening	Height
88.700	Obscure Glass	6 71031 00223 5	24"	64"



MUSTEE

E.L. Mustee & Sons, Inc. • 5431 West 164th Street • Brook Park, OH 44142 • Phone: 216.267.3100 • Fax: 216.267.9997
E-mail: info@mustee.com • Web: www.mustee.com • Proudly made in the USA

Notice: Our continuous commitment to product improvement may result in changes to product specifications without notice.
Patents pending. Made and Printed in U.S.A.