



Concrete Crack Filler

Flowable, polymer-based crack fill and seal for concrete surfaces

©TCC Materials • March 2016 • Version 1.1

PRODUCT DESCRIPTION

SAKRETE® Concrete Crack Filler is a ready-to-use, flowable polymer repair material, designed to fill and seal cracks in concrete up to ¼ in. wide and ¼ in. deep (6 mm x 6 mm).

WHEN/WHERE TO USE

For filling narrow holes/cracks in:

- Interior or exterior horizontal surfaces
- Driveways
- Steps
- Sidewalks
- Floors
- Patios

ADVANTAGES

- Ready-to-use (no mixing)
- Flexible
- Gray in color

PACKAGING

1 qt. (0.95 L) bottle (BOM 120026)

TYPICAL YIELD

One quart bottle will fill approximately 40 ft. (12.2 m) of crack at ¼ in. (6 mm) deep by ¼ in. (6 mm) wide.

SURFACE PREPARATION

Read all directions before starting work. Do not apply when temperatures are expected to fall below 50°F (10°C) within 24 hours. Clean area and remove all loose concrete, grease, oil, paint, dirt, and any foreign materials that will inhibit performance. Surface should be dry.

MIXING

Shake vigorously before using to ensure a uniform mix before application. Prior to use, place container in a warm location or submerge in hot water for better flowability.

APPLICATION

Cut applicator tip to size needed for repair. Squeeze Concrete Crack Filler into cracks. Troweling is not necessary. Deep cracks may require more than one application due to shrinkage during curing and will have extended drying times. Allow to dry overnight between applications. Do not apply to frozen surfaces. Protect from rain and water for 24 hours.

CLEAN UP

Warm, soapy water may be helpful for cleaning hands and tools.

NOTES AND LIMITATIONS

Air, mix, and substrate temperatures should be between 40°F-100°F (4°C- 37°C) with no rain in the forecast within 24 hours of application. Store tightly closed in original container in a dry place. KEEP FROM FREEZING.

Proper application and installation of all Sakrete products are the responsibility of the end user.

WARNING

WARNING! Avoid contact with eyes, skin and clothing. Wash thoroughly after handling. Exposure may result in irritation of the skin. FIRST AID: In case of eye contact, flush immediately with plenty of water for at least 15 minutes and get prompt medical attention; for skin, wash thoroughly with plenty of soap and water. KEEP OUT OF REACH OF CHILDREN. READ AND UNDERSTAND the Safety Data Sheet (SDS) before using this product.

LIMITED PRODUCT WARRANTY

The manufacturer warrants that this product shall be of merchantable quality when used or applied in accordance with the manufacturer's instructions. This product is not warranted as suitable for any purpose other than the general purpose for which it is intended. This warranty runs for one (1) year from the dates the product is purchased. ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ON THIS PRODUCT IS LIMITED TO THE DURATION OF THIS WARRANTY. Liability under this warranty is limited to replacement of defective products or, at the manufacturer's option, refund of the purchase price. CONSEQUENTIAL AND INCIDENTAL DAMAGES ARE NOT RECOVERABLE UNDER THIS WARRANTY.

SAKRETE® and the background design are registered trademarks of SAKRETE of North America LLC, Charlotte, NC 28273 • ©2006. SAKRETE® is manufactured under license from SAKRETE of North America LLC.

Shelf Life	One year in original, unopened container.
Storage Conditions	Store dry at 40-100°F (4°C -37°C).
Color	Gray.

Helpful Items:



Gloves



Pail



Water



Safety Glasses



Brush

KEEP FROM FREEZING

WARNING: INJURIOUS TO EYES

KEEP OUT OF REACH OF CHILDREN