



### Main

|                                       |                                       |
|---------------------------------------|---------------------------------------|
| Range of product                      | Modicon Premium Automation platform   |
| Bus type                              | Ethernet                              |
| Accessory / separate part category    | Connection accessories                |
| Accessory / separate part type        | Connecting cable                      |
| Accessory / separate part designation | Shielded twisted pair straight cable  |
| Accessory / separate part destination | Connection to data terminal equipment |
| Cable length                          | 6.56 ft (2 m)                         |
| Product certifications                | CSA 22-1                              |

### Complementary

|                       |   |
|-----------------------|---|
| Electrical connection | 2 connectors  |
| Connector type        | RJ45  |
| Flame retardance      | Class C2 conforming to CEI 322/1<br>Class C2 conforming to NF C 32070-1 |

### Environment

|           |   |
|-----------|---|
| Standards | EN 50173 class D<br>TIA-568 category 5<br>EIA-568 category 5<br>IEC 11801 class D |
|-----------|---|

### Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 18225 - PLC NTRK HRDWR & PROWORX SOFTWARE |
| Discount Schedule     | PC41                                      |
| GTIN                  | 00785901405658                            |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 0.25 lb(US) (0.11 kg)                     |
| Returnability         | Yes                                       |
| Country of origin     | TH  |

### Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Package 1 Height             | 0.59 in (1.5 cm)     |
| Package 1 width              | 7.48 in (19 cm)      |
| Package 1 Length             | 7.87 in (20 cm)      |
| Unit Type of Package 2       | S02                  |
| Number of Units in Package 2 | 20                   |
| Package 2 Weight             | 5.07 lb(US) (2.3 kg) |
| Package 2 Height             | 5.91 in (15 cm)      |
| Package 2 width              | 11.81 in (30 cm)     |
| Package 2 Length             | 15.75 in (40 cm)     |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| California proposition 65  | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>  |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| RoHS exemption information | <a href="#">Yes</a>   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|