

Garant
**UNC thread cutting set in a plastic case, for UNC unified coarse threads:
UNC1/4-3/4**

Order data

Order number	145955 UNC1/4-3/4
GTIN	4045197878571
Item class	11K

Description
Version:

Sturdy plastic case with carrying handle and 2 catches. Each tool is securely stored and protected in a foam insert and is immediately ready to hand. For more detailed descriptions of the content see individual products.

Application:

For UNC unified coarse threads ASME–B1.1.

Content:

- 1 set each hand tap No. 130700: Size 1/4; 5/16; 3/8; 7/16; 1/2; 5/8; 3/4
- 1 each die No. 142520: Size 1/4; 5/16; 3/8; 7/16; 1/2; 5/8; 3/4
- 1 each adjustable tap wrench No. 148410: Size 1.1/2; 2; 4
- 1 each die stock No. 149310: Size 20×7; 25×9; 30×11; 38×14; 45×18
- 1 screwdriver No. 664122: Size 5.5

Technical description

for UNC unified coarse threads	1/4 UNC - 3/4 UNC
Thread type	UNC

Flank angle	60 degrees
Type of product	Die

Accessories

Hand tap set UNC 3/8-16	130700 3/8-16
Die UNC 3/8-16	142520 3/8-16
Tap wrench, adjustable Type 4	148410 4
Hand tap set UNC 1/4-20	130700 1/4-20
Hand tap set UNC 1/2-13	130700 1/2-13
Die UNC 1/4-20	142520 1/4-20
Die stock for die $\varnothing \times$ height 20X7 mm	149310 20X7
Die UNC 5/8-11	142520 5/8-11
Die stock for die $\varnothing \times$ height 25X9 mm	149310 25X9
Tap wrench, adjustable Type 2	148410 2
Hand tap set UNC 7/16-14	130700 7/16-14
Die UNC 3/4-10	142520 3/4-10
Hand tap set UNC 5/16-18	130700 5/16-18
Die UNC 1/2-13	142520 1/2-13
Screwdriver for slot-head, short, with 2-component Haptoprene handle Blade width b 5,5 mm	664122 5,5
Die UNC 7/16-14	142520 7/16-14
Hand tap set UNC 5/8-11	130700 5/8-11
Tap wrench, adjustable Type 1.1/2	148410 1.1/2
Die stock for die $\varnothing \times$ height 45X18 mm	149310 45X18
Die stock for die $\varnothing \times$ height 38X14 mm	149310 38X14
Die UNC 5/16-18	142520 5/16-18
Die stock for die $\varnothing \times$ height 30X11 mm	149310 30X11
Hand tap set UNC 3/4-10	130700 3/4-10

