



Set of parallels, Length: 125mm



Order data

Order number	366704 125
GTIN	4045197761200
Item class	32D

Description

Version:

HOLEX – standard version. Height and pairing tolerance 0.01 mm. Stored in a wooden box (as shown on the illustration). Hardness: 60 HRC.

Precision ground as pairs.

Application:

In high precision work for parallel mounting of components in machine vices or jigs.

Content:

8×11; 8×16; 8×21; 8×26; 8×31; 8×36;
 10×13; 10×18; 10×23; 10×28; 10×33; 10×38;
 12×15; 12×20; 12×25; 12×30; 12×35; 12×40;
 14×17; 14×22; 14×27; 14×32; 14×37; 14×42

Note:

Sizes 125 – 200: In 1 mm increments, except 9 mm, all other dimensions achievable.
 See the spare parts list for spare holders.

Technical description

Length	125 mm
Number of strips	24 pair
Type of product	Pairs of parallels

Accessories

Single pair of parallels for 366702 / 6704 size 125 Width×height 14X42 mm	366711 14X42
Spare wooden case for pairs of parallels Type S2	366754 S2
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X40 mm	366711 12X40
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X15 mm	366711 12X15
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X35 mm	366711 12X35
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X20 mm	366711 12X20
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X17 mm	366711 14X17
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X18 mm	366711 10X18
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X38 mm	366711 10X38
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X13 mm	366711 10X13
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X22 mm	366711 14X22
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X11 mm	366711 8X11
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X16 mm	366711 8X16
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X21 mm	366711 8X21
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X27 mm	366711 14X27
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X36 mm	366711 8X36

Single pair of parallels for 366702 / 6704 size 125 Width×height 14X37 mm	366711 14X37
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X23 mm	366711 10X23
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X28 mm	366711 10X28
Single pair of parallels for 366702 / 6704 size 125 Width×height 14X32 mm	366711 14X32
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X26 mm	366711 8X26
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X30 mm	366711 12X30
Single pair of parallels for 366702 / 6704 size 125 Width×height 10X33 mm	366711 10X33
Single pair of parallels for 366702 / 6704 size 125 Width×height 12X25 mm	366711 12X25
Single pair of parallels for 366702 / 6704 size 125 Width×height 8X31 mm	366711 8X31