



Socket set 1/4 inch square drive 42 pieces, Type: 6



Order data

Order number	630329 6
GTIN	4062406230722
Item class	62A

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**.

Application:

For external hexagon screws / nuts with thread M2 – M8 and for hexagon socket head screws with thread M4 – M10.

For Pozidriv and Phillips screws with thread M2 – M6, slot-head screws with thread M2 – M4 and for internal Torx® screws with thread M2.5 – M8.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets single hexagon: 13 pcs. No. 631020 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

Bits, C 6.3, for hex socket: 4 pcs. similar to No. 675240 size 3; 4; 5; 6

Bits, C 6.3, for Phillips: 3 pcs. similar to No. 675310 size 1/25; 2/25; 3/25

Bits, C 6.3, for Pozidriv: 3 pcs. similar to No. 675320 size 1/25; 2/25; 3/25

Bits, C 6.3, for slot-head: 3 pcs. similar to No. 675250 size 3.5×0.6; 5.5×0.8; 8×1.2

Bits, C 6.3, for internal Torx®: 7 pcs. similar to No. 675340 size TX8; TX10; TX15; TX20; TX25; TX30; TX40

T-handle: 1 pc. similar to No. 633029 size 116

Spin type speeder: 1 pc. No. 632840 size 150

Extensions: 2 pcs. No. 632420 size 50; 100

Universal joint: 1 pc. No. 633520 size 1/4

Ratchet: 1 pc. No. 632090 size 1/4 with ejector

Adaptor E 6.3: 1 pc. similar to No. 675020 size 6.3K for 1/4 inch bits C 6.3

Converter: 1 pc. bit shank E 6.3 – square 1/4 inch

Bit adapter: 1 pc. No. 676800, 1/4 inch square – bit holder 1/4 inch

Storage in: ABS plastic box

Technical description

Drive profile	Hexagon screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Hexagon socket
Drive profile	Screwdriver for Phillips
Drive profile	Screwdriver for TORX® screws
Square drive	1/4 in
Width across flats range, hexagon wrenches	3-6 mm
Number of pieces	41
Width across flats range, hexagon sockets	4-14 mm
Packaging	ABS plastic box
Length	357 mm
Width	174 mm
Height	47 mm
Type of product	Socket spanner

Accessories

Adapter Type 4/4	676800 4/4
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675310 1/25
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX8	675340 TX8
Shank with magnet / quick-change coupling Hexagon shank 6,3K	675020 6,3K

Hexagon socket, 1/4 inch Width across flats 11 mm	631020 11
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675310 3/25
Bit for Phillips, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675310 2/25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 3 mm	675240 3
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX40	675340 TX40
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631020 4,5
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 1/25 mm	675320 1/25
Rigid foam inlay for set 630329	630324 630329
Reversible ratchet, 1/4 inch with ejector Type 1/4	632090 1/4
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX25	675340 TX25
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 6 mm	675240 6
Hexagon socket, 1/4 inch Width across flats 13 mm	631020 13
Hexagon socket, 1/4 inch Width across flats 14 mm	631020 14
Hexagon socket, 1/4 inch Width across flats 7 mm	631020 7
Hexagon socket, 1/4 inch Width across flats 9 mm	631020 9
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX30	675340 TX30
Modular box Type 2	630323 2
Spinner handle, 1/4 inch overall length 150	632840 150
T-handle, 1/4 inch overall length 116 mm	633029 116
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 3/25 mm	675320 3/25
Converter with ball Type 2	650005 2
Hexagon socket, 1/4 inch Width across flats 4 mm	631020 4
Bit for Pozidriv, 1/4 inch C 6.3 Cross-head size / overall length 2/25 mm	675320 2/25
Hexagon socket, 1/4 inch Width across flats 8 mm	631020 8
Extension, 1/4 inch overall length 100 mm	632420 100

Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 4 mm	675240 4
Hexagon socket, 1/4 inch Width across flats 10 mm	631020 10
Extension, 1/4 inch overall length 50 mm	632420 50
Hexagon socket, 1/4 inch Width across flats 12 mm	631020 12
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631020 5,5
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX15	675340 TX15
Hexagon socket, 1/4 inch Width across flats 5 mm	631020 5
Hexagon socket, 1/4 inch Width across flats 6 mm	631020 6
Bit for Torx®, 1/4 inch C 6.3 Torx® profile TX10	675340 TX10
Universal joint 1/4 inch Type 1/4	633520 1/4
Bit for hexagon, 1/4 inch C 6.3Hex-plus profile Hexagon 5 mm	675240 5