



Socket set 3/8 inch square drive 26 pieces, Type: 6



Order data

| | |
|--------------|---------------|
| Order number | 634318 6 |
| GTIN | 4062406230760 |
| Item class | 62A |

Description

Version:

Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124. Internal / external square drives to **DIN 3120**. With hexagon sockets No. 637220.

Application:

For hexagon head screws / nuts with thread M5 – M12, for spark plugs and for hexagon socket head screws with thread M4 – M12.

Material:

Chrome vanadium steel, chrome-plated.

Supplied with:

Sockets bi-hexagon or single hexagon: 12 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19 mm

Spark plug sockets: 2 pcs. similar to No. 637329 size 16; 20.8

Hexagon screwdriver bits: 7 pcs. No. 637620 size 3; 4; 5; 6; 7; 8; 10

T-handle: 1 pc. No. 635720

Extensions: 2 pcs. No. 635420 size 75; 240

Universal joint: 1 pc. No. 636220

Ratchet: 1 pc. No. 635090

Storage in: ABS plastic box

Technical description

| | |
|---|---------------------|
| Width across flats range, hexagon sockets | 8-19 mm |
| Drive profile | Hexagon screwdriver |

| | |
|--|-----------------|
| Drive profile | Hexagon socket |
| Number of pieces | 26 |
| Square drive | 3/8 in |
| Width across flats range, hexagon wrenches | 3-10 mm |
| Width across flats | metric |
| Packaging | ABS plastic box |
| Length | 357 mm |
| Width | 174 mm |
| Height | 47 mm |
| Type of product | Socket spanner |

Accessories

| | |
|---|---------------|
| Single hexagon socket for spark plugs 3/8 inch Width across flats 16 mm | 637329 16 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 8 mm | 637620 8 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 10 mm | 637620 10 |
| Extension, 3/8 inch overall length 75 mm | 635420 75 |
| T-handle, 3/8 inch overall length 200 mm | 635720 200 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 4 mm | 637620 4 |
| Modular box Type 3 | 630323 3 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 5 mm | 637620 5 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 3 mm | 637620 3 |
| Universal joint, 3/8 inch Type 3/8 | 636220 3/8 |
| Single hexagon socket for spark plugs 3/8 inch Width across flats 20,8 mm | 637329 20,8 |
| Screwdriver socket, hexagon, 3/8 inch Hexagon 6 mm | 637620 6 |
| Reversible ratchet, 3/8 inch with ejector Type 3/8 | 635090 3/8 |
| Rigid foam inlay for set 634318 | 630324 634318 |

Screwdriver socket, hexagon, 3/8 inch Hexagon 7 mm

637620 7