

Garant
Socket set 1/4 inch, Number of tools: 28

Order data

Order number	953624 28
GTIN	4062406155629
Item class	91A

Description
Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. **Upper layer is anthracite**, the underlying **contrast colour is grey**, thereby indicating any missing tools.

Supplied with:

Rigid foam inlay, empty No. 952001 size 953624: 1 pc.

GARANT ratchet No. 632025 size 1/4: 1 pc.

GARANT extension No. 632429 size 100; 150: 1 pc. each

GARANT spinner handle No. 632829 size 146: 1 pc.

GARANT T-handle No. 633029 size 116: 1 pc.

GARANT universal joint No. 633529 size 1/4: 1 pc.

GARANT hexagon key L-wrench set No. 627132 size 9: 1 pc.

GARANT hexagon socket No. 631029 size 3.5; 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13: 1 pc. each

Technical description

Depth in G	16
Depth	400 mm
Width	150 mm
Number of tools	28
Weight	1.025 kg
Width in G	6

Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	6×16
Square drive	1/4 in
Type of product	Rigid foam inlay

Accessories

Hexagon socket, 1/4 inch Width across flats 7 mm	631029 7
Extension, 1/4 inch overall length 100 mm	632429 100
Hexagon socket, 1/4 inch Width across flats 12 mm	631029 12
Hexagon key L-wrench set, with retainer ballchrome-plated Number of screwdrivers 9	627132 9
Spinner handle, 1/4 inch overall length 146 mm	632829 146
Hexagon socket, 1/4 inch Width across flats 10 mm	631029 10
Hexagon socket, 1/4 inch Width across flats 6 mm	631029 6
Rigid foam inlay for tool sets suitable for rigid foam set 953624	952001 953624
Hexagon socket, 1/4 inch Width across flats 3,5 mm	631029 3,5
Extension, 1/4 inch overall length 150 mm	632429 150
Hexagon socket, 1/4 inch Width across flats 4 mm	631029 4
Hexagon socket, 1/4 inch Width across flats 11 mm	631029 11
T-handle, 1/4 inch overall length 116 mm	633029 116
Hexagon socket, 1/4 inch Width across flats 9 mm	631029 9
Universal joint 1/4 inch Type 1/4	633529 1/4
Reversible ratchet, 1/4 inch with ejector Type 1/4	632025 1/4
Hexagon socket, 1/4 inch Width across flats 5,5 mm	631029 5,5
Hexagon socket, 1/4 inch Width across flats 8 mm	631029 8
Hexagon socket, 1/4 inch Width across flats 4,5 mm	631029 4,5

Hexagon socket, 1/4 inch Width across flats 5 mm	631029 5
Hexagon socket, 1/4 inch Width across flats 13 mm	631029 13