



Socket set 3/8 inch, Number of tools: 24



Order data

Order number	953710 24
GTIN	4062406157159
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for :

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Foam inlays of size 10 G × 8 G suit shadowboards No. 923210 size 250 (2 foam inlays per shadowboard).

Supplied with:

Rigid foam inlay, empty No. 952001 size 953710: 1 pc.

HOLEX hexagon socket No. 637220 size 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19: 1 pc. each

HOLEX hexagon screwdriver bit No. 637620 size 3; 4; 5; 6; 8; 10: 1 pc. each

HOLEX reversible ratchet, No. 635090 size 3/8: 1 pc.

HOLEX extension No. 635420 size 75; 125: 1 pc. each

HOLEX T-handle No. 635720 size 200: 1 pc.

HOLEX universal joint No. 636220 size 3/8: 1 pc.

Square drive: 3/8 in

Width: 200 mm

Depth: 250 mm
 Width in G: 8
 Depth in G: 10
 Weight: 1.384 kg

Technical description

Width	200 mm
Width in G	8
Number of tools	24
Depth in G	10
Depth	250 mm
Weight	1.384 kg
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x10
Square drive	3/8 in
Type of product	Rigid foam inlay

Accessories

Hexagon screwdriver bit, 3/8 inch Hexagon 4 mm	637620 4
Hexagon screwdriver bit, 3/8 inch Hexagon 6 mm	637620 6
Hexagon screwdriver bit, 3/8 inch Hexagon 10 mm	637620 10
Hexagon socket, 3/8 inch Width across flats 19 mm	637220 19
Hexagon screwdriver bit, 3/8 inch Hexagon 5 mm	637620 5
Hexagon screwdriver bit, 3/8 inch Hexagon 8 mm	637620 8
Extension, 3/8 inch overall length 125 mm	635420 125
Extension, 3/8 inch overall length 75 mm	635420 75
Rigid foam inlay for tool sets suitable for rigid foam set 953710	952001 953710
Hexagon socket, 3/8 inch Width across flats 13 mm	637220 13

Hexagon socket, 3/8 inch Width across flats 9 mm	637220 9
Hexagon socket, 3/8 inch Width across flats 15 mm	637220 15
Hexagon socket, 3/8 inch Width across flats 12 mm	637220 12
Hexagon socket, 3/8 inch Width across flats 7 mm	637220 7
T-handle, 3/8 inch overall length 200 mm	635720 200
Universal joint, 3/8 inch Type 3/8	636220 3/8
Hexagon socket, 3/8 inch Width across flats 14 mm	637220 14
Hexagon socket, 3/8 inch Width across flats 10 mm	637220 10
Reversible ratchet, 3/8 inch with ejector	635120
Reversible ratchet, 3/8 inch with ejector Type 3/8	635090 3/8
Hexagon socket, 3/8 inch Width across flats 18 mm	637220 18
Hexagon socket, 3/8 inch Width across flats 11 mm	637220 11
Hexagon screwdriver bit, 3/8 inch Hexagon 3 mm	637620 3
Hexagon socket, 3/8 inch Width across flats 17 mm	637220 17
Hexagon socket, 3/8 inch Width across flats 16 mm	637220 16
Hexagon socket, 3/8 inch Width across flats 8 mm	637220 8