



## Socket set 1/2 inch square drive 33 pieces, Type: 12



### Order data

Order number	638018 12
GTIN	4062406230852
Item class	62A

### Description

#### Version:

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120**.

With bi-hexagon sockets No. 642120.

#### Application:

For hexagon head screws / nuts with thread M6 – M22 and hexagon socket head screws with thread M5 – M18.

#### Material:

Chrome vanadium steel, chrome-plated.

#### Supplied with:

Sockets: 19 pcs. size 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32; 34 mm

Hexagon screwdriver bits: 8 pcs. No. 643220 size 4; 5; 6; 7; 8; 10; 12; 14

T-handle: 1 pc. 641320 size 295

Extensions: 3 pcs. No. 641020 75; 125; 250

Universal joint: 1 pc. No. 641620 size 1/2

Ratchet: 1 pc. No. 640190 size 1/2

Storage in: ABS plastic box

### Technical description

Square drive	1/2 in
Number of pieces	33

Width across flats range, hexagon sockets	8-34 mm
Width across flats range, hexagon wrenches	4-14 mm
Width across flats	metric
Length	507 mm
Width	227 mm
Height	62 mm
Type of product	Socket spanner

## Accessories

Modular box Type 5	630323 5
Rigid foam inlay for set 638018	630324 638018
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Extension, 1/2 inch overall length 130 mm	641020 130
Extension, 1/2 inch overall length 75 mm	641020 75
T-handle, 1/2 inch overall length 295 mm	641320 295
Universal joint, 1/2 inch Type 1/2	641620 1/2
Hexagon bit socket, 1/2 inch Hexagon 10 mm	643220 10
Hexagon bit socket, 1/2 inch Hexagon 12 mm	643220 12
Hexagon bit socket, 1/2 inch Hexagon 14 mm	643220 14
Hexagon bit socket, 1/2 inch Hexagon 4 mm	643220 4
Hexagon bit socket, 1/2 inch Hexagon 5 mm	643220 5
Hexagon bit socket, 1/2 inch Hexagon 6 mm	643220 6
Hexagon bit socket, 1/2 inch Hexagon 7 mm	643220 7
Hexagon bit socket, 1/2 inch Hexagon 8 mm	643220 8