



Expansion set 3/8 inch, Number of tools: 17



Order data

Order number	953714 17
GTIN	4067263723592
Item class	91A

Description

Version:

Popular tool sets in two-colour PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer is anthracite, the underlying contrast colour is grey, thereby indicating any missing tools.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Foam inlays of size 10 G × 8 G suit shadowboards No. 923210 size 250 (2 foam inlays per shadowboard).

Supplied with:

HOLEX bi-hexagon socket No. 637320 size 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22: 1 pc. each

HOLEX hexagon screwdriver bit extra long No. 637613 size 4; 5; 6; 8; 10: 1 pc. each

Rigid foam inlay, empty No. 952001 size 953714: 1 pc.

Technical description

Depth	250 mm
Depth in G	10

Width	200 mm
Version	with socket
Width in G	8
Number of tools	17
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8×10
Square drive	3/8 in
Type of product	Rigid foam inlay

Accessories

Rigid foam inlay for tool sets suitable for rigid foam set 953714	952001 953714
Bi-hexagon socket, 3/8 inchdeep Width across flats 10 mm	637320 10
Bi-hexagon socket, 3/8 inchdeep Width across flats 11 mm	637320 11
Bi-hexagon socket, 3/8 inchdeep Width across flats 12 mm	637320 12
Bi-hexagon socket, 3/8 inchdeep Width across flats 13 mm	637320 13
Bi-hexagon socket, 3/8 inchdeep Width across flats 14 mm	637320 14
Bi-hexagon socket, 3/8 inchdeep Width across flats 15 mm	637320 15
Bi-hexagon socket, 3/8 inchdeep Width across flats 16 mm	637320 16
Bi-hexagon socket, 3/8 inchdeep Width across flats 17 mm	637320 17
Bi-hexagon socket, 3/8 inchdeep Width across flats 18 mm	637320 18
Bi-hexagon socket, 3/8 inchdeep Width across flats 19 mm	637320 19
Bi-hexagon socket, 3/8 inchdeep Width across flats 21 mm	637320 21
Bi-hexagon socket, 3/8 inchdeep Width across flats 22 mm	637320 22
Screwdriver socket, hexagon, 3/8 inchlong, with ball point Hexagon 10 mm	637613 10
Screwdriver socket, hexagon, 3/8 inchlong, with ball point Hexagon 4 mm	637613 4
	637613 5

Screwdriver socket, hexagon, 3/8 inch long, with ball point
Hexagon 5 mm

Screwdriver socket, hexagon, 3/8 inch long, with ball point
Hexagon 6 mm

637613 6

Screwdriver socket, hexagon, 3/8 inch long, with ball point
Hexagon 8 mm

637613 8