

**Garant**
**Socket set 1/4 inch square drive 41 pieces, Type: SD**

**Order data**

Order number	630325 SD
GTIN	4062406060282
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

System box of virtually indestructible ABS plastic with integral hinges and innovative, easy-to-use snap fastener. All tools are held securely for easy access in a specially moulded **PUR foam insert.**

The Surface Drive profile works directly on the faces of the nuts and bolts; weaker corners are protected. Even intermediate sizes (e.g. inch size bolts) and worn bolt heads can be tightened or released using the Surface Drive profile. The Wobble-Fix extensions allow use at an angle and can be secured by clicking into place.

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.**

**Application:**

For external hexagon screws / nuts with thread M2 – M8 and for hexagon socket head screws with thread M4 – M10.

For Pozidriv and Phillips screws with thread M2 – M6, slot-head screws with thread M2 – M4 and for internal Torx® screws with thread M2.5 – M8.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Surface Drive hexagon sockets: 13 pcs. No. 631225 size 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13; 14

Bits, C 6.3, for hex socket: 4 pcs. similar to No. 675240 size 3; 4; 5; 6

Bits, C 6.3, for Phillips: 3 pcs. similar to No. 675310 size 1/25; 2/25; 3/25

Bits, C 6.3, for Pozidriv: 3 pcs. similar to No. 675320 size 1/25; 2/25; 3/25

Bits, C 6.3, for slot-head: 3 pcs. similar to No. 675250 size 3.5×0.6; 5.5×0.8; 8×1.2  
 Bits, C 6.3, for internal Torx®: 6 pcs. similar to No. 675340 size TX10; TX15; TX20; TX25; TX30; TX40  
 T-handle: 1 pc. No. 633029 size 116  
 Spin type speeder: 1 pc. 632829 size 146  
 Extensions "Wobble-Fix": 2 pcs. 632519 size 50; 100  
 Universal joint: 1 pc. No. 633529 size 1/4  
 Ratchet: 1 pc. No. 632025 size 1/4 with ejector  
 Adaptor E 6.3: 1 pc. similar to No. 675020 size 6.3K for 1/4 inch bits C 6.3  
 Converter: 1 pc. bit shank E 6.3 – square 1/4 inch  
 Bit adapter: 1 pc. similar to No. 676800, 1/4 inch square socket – bit holder 1/4 inch  
 Presented in: ABS plastic box

## Technical description

Number of pieces	41
Width across flats range, hexagon wrenches	3-6 mm
Width across flats range, Surface Drive	4-14 mm
Drive profile	Hexagon socket Surfacedrive
Drive profile	Screwdriver for Phillips
Drive profile	Pozidriv screwdriver
Drive profile	Pozidriv screwdriver
Drive profile	Screwdriver for TORX® screws
Square drive	1/4 in
Hexagon socket profile	Surfacedrive
Square with Wobble-Fix	with angle of inclination
Packaging	ABS plastic box with quick release fastener.
Length	257 mm
Width	147 mm
Height	45 mm
Degree of fill of a drawer in units	5×10
Type of product	Socket spanner

## Accessories

PUR foam inlay for set 630325	630304 630325
Modular box Type 2	630305 2
Hexagon socket, 1/4 inchSurface Drive Width across flats 7 mm	631225 7
Hexagon socket, 1/4 inchSurface Drive Width across flats 12 mm	631225 12
T-handle, 1/4 inch overall length 116 mm	633029 116
Reversible ratchet, 1/4 inch with ejector Type	632025
Hexagon socket, 1/4 inchSurface Drive Width across flats 6 mm	631225 6
Hexagon socket, 1/4 inchSurface Drive Width across flats 10 mm	631225 10
Hexagon socket, 1/4 inchSurface Drive Width across flats 13 mm	631225 13
Hexagon socket, 1/4 inchSurface Drive Width across flats 11 mm	631225 11
Hexagon socket, 1/4 inchSurface Drive Width across flats 4 mm	631225 4
Hexagon socket, 1/4 inchSurface Drive Width across flats 9 mm	631225 9
Universal joint 1/4 inch Type 1/4	633529 1/4
Hexagon socket, 1/4 inchSurface Drive Width across flats 5 mm	631225 5
Hexagon socket, 1/4 inchSurface Drive Width across flats 8 mm	631225 8
Hexagon socket, 1/4 inchSurface Drive Width across flats 5,5 mm	631225 5,5
Hexagon socket, 1/4 inchSurface Drive Width across flats 14 mm	631225 14
Hexagon socket, 1/4 inchSurface Drive Width across flats 4,5 mm	631225 4,5
Spinner handle, 1/4 inch overall length 146 mm	632829 146

Extension, 1/4 inch "Wobble-Fix" overall length 50 mm	632519 50
Extension, 1/4 inch "Wobble-Fix" overall length 100 mm	632519 100