

**Garant**
**Socket set 3/8 inch square drive 25 pieces, Type: 12**

**Order data**

Order number	634312 12
GTIN	4062406060770
Item class	61A

**Description**
**Version:**

**Drives / accessories to DIN 3122 / 3123; sockets to DIN 3124.** Internal / external square drives to **DIN 3120.**

All tools are held securely for easy access in a specially moulded hard-wearing **PUR foam inlay.** With bi-hexagon sockets No. 637029.

**Application:**

For hexagon head screws / nuts with thread M5 – M12, for spark plugs and for hexagon socket head screws with thread M4 – M12.

**Material:**

Chrome vanadium steel, chrome-plated.

**Supplied with:**

Sockets bi-hexagon or single hexagon: 11 pcs. size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19 mm

Spark plug sockets: 2 pcs. No. 637329 size 16; 20.8

Hexagon screwdriver bits: 7 pcs. No. 637629 size 3; 4; 5; 6; 7; 8; 10

T-handle: 1 pc. No. 635729

Extensions: 2 pcs. No. 635429 size 75; 240

Universal joint: 1 pc. No. 636229

Ratchet: 1 pc. No. 635025

Storage in: ABS plastic box

**Technical description**

Square drive	3/8 in
--------------	--------

Drive profile	Bi-hex socket
Drive profile	Hexagon screwdriver
Width across flats range, bi-hex sockets	8-19 mm
Width across flats range, hexagon wrenches	3-10 mm
Packaging	ABS plastic box
Length	357 mm
Width	176 mm
Height	45 mm
Degree of fill of a drawer in units	6×14
Type of product	Socket spanner

## Accessories

Modular box Type 3A	630305 3A
PUR foam inlay for set 634312	630304 634312
Single hexagon socket for spark plugs 3/8 inch Width across flats 16 mm	637329 16
Screwdriver socket, hexagon, 3/8 inch Hexagon 5 mm	637629 5
Extension, 3/8 inch overall length 75 mm	635429 75
Extension, 3/8 inch overall length 240 mm	635429 240
Single hexagon socket for spark plugs 3/8 inch Width across flats 20,8 mm	637329 20,8
Screwdriver socket, hexagon, 3/8 inch Hexagon 8 mm	637629 8
Screwdriver socket, hexagon, 3/8 inch Hexagon 4 mm	637629 4
Screwdriver socket, hexagon, 3/8 inch Hexagon 6 mm	637629 6
Reversible ratchet, 3/8 inch with ejector Type	635025
T-handle, 3/8 inch overall length 200 mm	635729 200
Universal joint, 3/8 inch Type 3/8	636229 3/8
Screwdriver socket, hexagon, 3/8 inch Hexagon 10 mm	637629 10

Screwdriver socket, hexagon, 3/8 inch Hexagon 3 mm	637629 3
Screwdriver socket, hexagon, 3/8 inch Hexagon 7 mm	637629 7