

PIG® Economy 2-Drum Poly Spill Containment Pallet

PAK605 Holds (2) 55 gal. Steel Drums, 29.9" x 54.6" x 16.8", Sump Capacity 66 gal.

This cost-effective drum pallet shares many features with our more expensive models - plus it's made from recycled content!

- These pallets may be economical, but they're strong enough to handle long-term storage of fully loaded steel drums
- Low-density polyethylene (LDPE) construction resists UV rays, rust, corrosion and most chemicals
- Textured grating adds traction and lifts out for easy sump access
- 2-way forklift entry allows easy movement from either direction (unloaded only)
- Optional .75" drain plug lets you empty sump without removing drums or grating
- We test all of our Containment Pallet designs at max load for months to ensure they can handle full capacity at your facility



Item#	Description	Dimensions	Weight
PAK605-WD	With Drain	29.9" W x 54.6" L x 16.8" H	62 lbs.
PAK605-WOD	Without Drain	29.9" W x 54.6" L x 16.8" H	62 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK605-WD	With Drain	76cm W x 139cm L x 43cm H	28.1 kg
PAK605-WOD	Without Drain	76cm W x 139cm L x 43cm H	28.1 kg

Specifications

Sump Capacity Range	40 - 69.9 gal.
Dimensions	29.9" W x 54.6" L x 16.8" H
Recycled Content	97% Post-Industrial Recycled Polyethylene
Load Capacity UDL	1500 lbs.
Sump Capacity	66 gal.
Brand	PIG
Color	Black

Drain	Optional .75" Drain
Double-Stackable Unit	No
Grates	(1) 48" L x 24" W Grate
Fork Truck Access	Two-Way Fork Access, Move Unloaded Only
Holds	(2) 55 gal. Steel Drums
Material	Poly
Use With Flammables	No
Sold as	1 each
Weight	62 lbs.
# per Pallet	6
Composition	Sump: Polyethylene (LDPE) w/ UV Inhibitor Grate: Polyethylene
UNSPSC	24101905
Pigalog® Page Number	<u>Page 350</u>

Metric Equivalent

Sump Capacity	249.8 L
Load Capacity UDL	680.4 kg
Weight	28.1 kg
Dimensions	76cm W x 139cm L x 43cm H

Technical Information

Technical Documents

LDPE Products

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com