



## PIG® Absorbent Barrel Top Safety Message Mat with Poly Backing

SGN1208 Waste Oil, For 55 gal. drums with 2 bungs (2" Dia.), 25 pads per box

Convey critical alerts and keep your poly drum tops clean with these leak-proof message mats.

- Barrel-top message mats warn or direct workers, beyond just drum contents, while also preventing dirty drum tops
- Ideal for chemical companies, waste facilities, manufacturing plants and other industrial setting
- Fit standard poly drums with perfectly sized cutouts for bungs
- Absorb liquid drips, drops and spills
- Leak-proof poly-backing blocks seeping liquids to prevent dirty drums
- Bright imagery is easily legible and stands out to give you confidence that the message will be noticed
- Top location of message remains visible even when drums are grouped in storage with sides covered by other drums
- Messages can convey more than just contents of drum thanks to New Pig's printing capability, the first of its kind in the Absorbents industry
- Durable construction of heavyweight mat lasts over many uses
- Mats take on the properties of absorbed liquids, so always take proper precautions when handling saturated absorbents



### Specifications

<b>Absorbency Range</b>	1 - 9.9 gal.
<b>Use With</b>	55 gal. drums with 2 bungs (2" Dia.)
<b>Dimensions</b>	ext. dia. 22"
<b>Mat Weight</b>	Heavyweight
<b>Absorbency</b>	Up to 6.62 gal. per box
<b>Absorbency per</b>	Up to 33.9 oz. per pad
<b>Brand</b>	PIG
<b>Bung Opening</b>	2" & 2"

<b>Category</b>	Barrel Top Absorbent Mat Sign
<b>Drum Type</b>	Poly Drum
<b>Drum Size</b>	55 gal.
<b>Flammability Specifications</b>	Flame Resistant - Will melt and self-extinguish
<b>Fluid Absorbed</b>	Oils; Coolants; Solvents; Water; Universal
<b>Indoor/Outdoor</b>	Indoor Use
<b>Incinerable</b>	Yes
<b>Legend</b>	Waste Oil
<b>Reusable</b>	No
<b>Special Feature</b>	Poly-Backing
<b>Static-Dissipative</b>	No
<b>UV Resistant</b>	No
<b>Wringable</b>	Yes
<b>Sold as</b>	25 pads per box
<b>Weight</b>	6.6 lbs.
<b># per Pallet</b>	72
<b>Composition</b>	Polypropylene
<b>UNSPSC</b>	47131901

## Metric Equivalent

<b>Absorbency per</b>	Up to 1002.4 mL per pad
<b>Absorbency</b>	Up to 25.1 L per box
<b>Weight</b>	3 kg
<b>Dimensions</b>	ext. dia. 56cm

## Technical Information



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)