



PIG® Magnetic Roof Leak Diverter Tarp

TLS1998 20" x 20", Leak Diverter Tarp, Install With Magnets

Quickly respond to metal roof and ceiling leaks with a customizable, magnetic fit, even in hard-to-access areas

- Easily keep rain and snow from storming *inside*. Whether condensation and ice, or heavy rain from a high-wind hurricane, this solution will quickly protect your team and what you've built.
- Sewn-in magnets allow for easy, fast deployment anywhere that metal is present
- Magnets provide a customized fit in areas where traditional leak diverter tarps may be difficult to hang
- Heavy-duty vinyl-coated tarp resists punctures, UV and mildew and lasts multiple deployments
- Pinched corners create a funnel to channel liquids to a drain or collection container without overflowing or sagging; engineered with leak-proof seams and connections
- Diverter tarp can hold up to 50 lbs. or 6 gallons using magnets alone; grommets along the sides provide extra support in high-flow situations
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- Hose (required), hanging straps (optional) and collection container (optional) sold separately

Item#	Description	Dimensions	Weight
TLS1998-BK		20" W x 20" L	1.54 lbs.
TLS1998-WH		20" W x 20" L	1.54 lbs.
TLS1998-YW		20" W x 20" L	1.54 lbs.

Metric Equivalent:

Item#	Description	Dimensions	Weight
TLS1998-BK		51cm W x 51cm L	.7 kg
TLS1998-WH		51cm W x 51cm L	.7 kg
TLS1998-YW		51cm W x 51cm L	.7 kg

Specifications

Dimensions	20" W x 20" L
Application	Roofs; Pipes
Brand	PIG
Contains	Leak Diverter Tarp

Drainage Hose	Sold Separately
Flow Rate	3.33 gal./Minute
Hanging Straps	Not Required
Hose Connector	.75" w/ Quick Connect
Installation Method	Magnets
Shape	Square
Sold as	1 each
Weight	1.54 lbs.
Composition	Diverter (Colors): PVC, Polyester Leak Diverter (Clear): PVC w/ Polyester Reinforcement Magnets: Neodymium Grommets: Brass
Includes	1 - 20" W x 20" L Leak Diverter Tarp 1 - Hose Connector Replacement Set (TLS745)
UNSPSC	24141506
Pigalog® Page Number	<u>Page 248</u>

Metric Equivalent

Weight	.7 kg
Dimensions	51cm W x 51cm L

Technical Information

Technical Documents

[Instructions for PIG Magnetic Leak Diverter Systems](#)



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com