



# INSTALLATION

**PIONEER INDUSTRIES, INC.**  
 3325 S. Garfield Ave.  
 Commerce, CA 90040  
 (800) 338-9468  
 www.pioneerind.com

### Tools:



Adjustable Wrench



Plumbers Putty



Teflon Tape



Rags

**Model Number:** 3LG260H, 3LG260H-WD, 3LG262BH,  
 3LG264H, 3LG264H-WD, 3LG264GH, 3LG264GH-WD




### Warnings and Notes:


Check with local plumbing code requirements before installation.  
 This product should be installed by a local listed plumber.  
**Do not use plumbers putty on threads.**

### Installation Steps:


Single Handle Lavatory Faucet




(1) Shut off water supplies. Remove old faucet. Clean mounting surface in preparation for new faucet.



(2) Place washer (for 1-hole installation) or deck cover plate (for 3-hole installation) on the bottom of faucet. Lead inlet hoses through mounting hole, slide mounting plates through mounting bolts and tighten with mounting nut from underneath the sink.




(3) Connect hot and cold inlet supply hoses to supply stops. For 1/2" connection; use 3/8" male to 1/2" female adapter for installation. Adapters are optional and not provided with faucet. Turn on both side supply stops.




(4) Important: After installation is complete, remove aerator. Turn water supplies on and allow both hot and cold water to run at least one minute each. While water is running, check for leaks. Turn off water and replace aerator.


### Pop-up Drain Installation:




(1) Remove pop-up flange from body




(2) Place a ring of plumbers putty on the bottom of flange.




(3) Insert pop-up flange through drain hole and attach flange to body. Use Teflon tape to thread tail piece to Pop-up drain body. Ensure the pop-up outlet faces towards the back of the sink. Tighten the locknut securely with a wrench. Do not overtighten.




(4) Remove the excess plumbers putty. Connect the trap (check manufacturer's instructions for installation).



(5) Remove pivot rod nut from pop-up body, ensure the washers is in place, insert pivot rod, tighten pivot rod nut back to pop-up body.



(6) Push pivot rod down, insert drain plug carefully. Test to ensure drain plug works properly.




(7) Connect lift rod strap to pivot rod by using clip. Tighten the thumbscrew to connect lift rod strap to pop-up lift rod.

## Exploded Drawing :

\* Note: Please specify finish/color when ordering.

	ITEM #	DESCRIPTION
A	X-1300001*	Lever Handle
B	X-4900017*	Cap
C	X-4900018	Locknut
D	X-3900003	Ceramic Disc Cartridge
E	X-4300024*	Hole Cover (For "4" Suffix)
F	OP-490065*	1.2 GPM Aerator
G	X-4200076	Washer
H	X-5300007	Mounting Kit
I	X-4300038*	Deck Cover Plate (For "WD" Suffix)
J	X-6300001*	Brass Pop-Up Drain Assembly (For "0" Suffix)
K	X-6300023*	50/50 Drain Assembly (For "2" Suffix)
L	X-6300002*	Brass Grid Strainer (For "G" Suffix)
1	X-4900001	Red/Blue Index Button
2	X-4900002	Allen Screw



For more care information or trouble shooting inquiries about your Pioneer product, please call:  
**Pioneer Industries, Inc.** (800) 338-9468  
 Monday-Friday 8 AM to 8 PM EST (5 AM to 5 PM PST)  
[www.pioneerind.com](http://www.pioneerind.com)