

V-DrillGuide® DRILL BIT GUIDE



Heat-Treated Steel
This heat-treatment throughout the *entire* guide allows for a tight tolerance and stronger tool to clamp

The "V-groove" Bottom
This design on the bottom allows accurate alignment of drill bits on corners and round surfaces

Drill Straight - Every Time!

Alignment Marks
Marks on both sides of guide to help align the guide - precision!


Flat Base
Able to use on flat surfaces



Easy to Use
Hold the drill guide on the material, clamp and drill



Warranty - Lifetime Warranty



**Use on
Corners**

**Use on
Round Pieces**

**Use on
Flat Materials**



V-DrillGuide® - DRILL BIT GUIDE

V-DrillGuide - the drill guide is like a portable drill press. This tool allows you to drill straight. Use this on corners, round or flat materials. Various sizes available. Heat-treated steel for durability. 100% USA-made. Drill straight, every time!

V-DrillGuide®



DRILL BIT GUIDE:

AVAILABLE SIZES:

SKU	Hole Sizes	Standard/Metric
STD3000DGNP	33/64", 17/32", 35/64", 9/16", 37/64", 19/32", 39/64", 5/8"	Standard
STD2000DGNP	3/8, 25/64, 13/32, 27/64, 7/16, 29/64, 15/32, 31/64, 1/2"	Standard
STD1000DGNP	1/8, 9/64, 5/32, 11/64, 3/16, 13/64, 7/32, 15/64, 1/4, 17/64, 9/32, 19/64, 5/16, 21/64, 11/32, 23/64, 3/8"	Standard
SDGMINI	#10, 21, 25, 29, 30, 1/8", 33, 7/64", 36, 37, 38, 40, 3/32", 43, 45, 47, 5/64", 50, 1/16", 53, 3/64"	Standard
MDG2000NP	10, 10.5, 11, 11.5, 12, 12.5, 13, 13.5, 14	Metric
MDG1000NP	3, 3.3, 3.5, 4, 4.2, 4.5, 5, 5.5, 6, 6.5, 6.8, 7, 7.5, 8, 8.5, 9, 9.5mm	Metric

V-TapGuide®



TAP GUIDE

AVAILABLE SIZES:

SKU	Hole Sizes	Standard/Metric
STD500NP	0-80, 1/64, 1-72, 2-56, 2-64, 3-48, 3-56, 4-36, 4-40, 4-48, 5-40, 5-44, 6-32, 6-36, 6-40, 8-32, 8-36, 8-40, 10-24, 10-32, 1/4-20, 1/4-28, 5/16-18, 5/16-24, 3/8-16, 3/8-24, 7/16-14, 7/16-20, 1/2-13, 1/2-20, 5/8-11, 5/8-18"	Standard
MTG500NP	1.6, 2, 2.5, 3, 3.5, 4, 5, 6, 8, 10, 12, 14, 16mm	Metric
STI-UNC100SNP	9/16-12, 1/2-13, 7/16-14, 3/8-16, 5/6-18, 1/4-20, 12-24, 10-24, 8-32, 6-32"	Standard
STI-UNF200SNP	5/8-18, 9/16-18, 1/2-20, 7/16-20, 3/8-24, 5/6-24, 1/4-28, 10-32, 8-36"	Standard

BUNDLE SETS



AVAILABLE SIZES:

SKU	Tools Included	Standard/Metric
BGTULTIMATESET	All tools listed above: STD3000DGNP, STD2000DGNP, STD1000DGNP, SDGMINI, MDG2000NP, MDG1000NP, STD500NP, MTG500NP, STI-UNC100SNP, STI-UNF200SNP	Standard/Metric
BGTDRILLSET	STD3000DGNP, STD2000DGNP, STD1000DGNP, SDGMINI, MDG2000NP, MDG1000NP	Standard/Metric
BGTTAPSET	STD500NP, MTG500NP, STI-UNC100SNP, STI-UNF200SNP	Standard/Metric
BGTSTANDARDSET	STD3000DGNP, STD2000DGNP, STD1000DGNP, SDGMINI, STD500NP, STI-UNC100SNP, STI-UNF200SNP	Standard
BGTMETRICSET	MDG2000NP, MDG1000NP, MTG500NP	Metric



Each tool includes
FREE storage cases!

