

RETRACTABLE NOZZLE VACUUM SEALER W/ GAS FLUSH

AVN-SERIES

sealersales

Gas Flush w Speed at 6CFM



- 100% Maintenance Free Venturi Vacuum Pump
- Intuitive Design
- Extensive Safety Features
- Rust Treated Powder Coated Steel Chassis
- Clean Room Compatible
- Two Year Warranty

MADE IN THE USA

Our **AVN-Series** delivers a leak proof seal on a variety of flexible bags including clear, foil (Mylar), mil spec and ESD bags. With one touch of the pedal, the AVN flushes out oxygen and moisture with nitrogen or any other inert gas to protect and extend the life of your product. This quality vacuum sealer is also great for reducing the bulk of items or keeping them from wear due to friction during transportation.

The AVN is also ideal for dry packaging applications on trays, tape and reel, tubes, and a variety of SMD shipping containers. Of key significance, the AVN-Series vacuum sealers will not fire an impulse until the upper and lower jaw completely meet, further ensuring operator safety and uncompromised seal integrity. Combine the AVN's precise automation with speed, extensive safety features, and incredible durability, the AVN-Series is ideal for the food, pharmaceutical, medical or electronic industry. Providing additional functionality and convenience, the AVN's gas flush or vacuum functions can be switched off for impulse sealing only.

The AVN is hand assembled using only superior grade components. It features five seal lengths (20", 25", 30", 35", 50") and can be custom configured to meet CE certification requirements.

SPECIFICATIONS	AVN-20	AVN-25	AVN-30	AVN-35	AVN-50
SEALING LENGTH	20"	25"	30"	35"	50"
SEAL WIDTH	1/4"	1/4"	1/4"	1/4"	1/4"
AIR REQUIREMENTS	6CFM@100PSI	6CFM@100PSI	6CFM@100PSI	6CFM@100PSI	12CFM@100PSI
VACUUM FLOW (CFM)	6	6	6	6	6
MAX VAC PRESSURE (inHG)	27	27	27	27	27
AMPS@120 VOLTS AC	8	9	13	15	15
DIMENSIONS (LxWxH)	25" x 10" x 7"	33" x 10" x 7"	38" x 10" x 7"	43" x 10" x 7"	64" x 10" x 7"
WEIGHT (LB)	35 / 40	41 / 47	55 / 62	62 / 72	100 / 111



Optional
Work Tray

ADDITIONAL OPTIONS

- Bi-Active Seal
- Stainless Steel Upgrade
- CE Certification
- Vacuum Filter
- Vacuum Regulator
- Voltage: 220V
- Dual Nozzle - standard for AVN-50
- Digital Temperature Controller
- Working Tray - 20" x 12"