

### Features

- Two-piece design.
- Round-front bowl offers an ideal solution for smaller bathrooms and powder rooms.
- Right-hand nested trip lever offers a choice of 1.1 or 1.6 gallons per flush (gpf).
- 2-1/8" (54 mm) fully glazed trapway.
- Coordinates with other products in the Wellworth collection.
- Combination consists of the K-4197 bowl and the K-4458-RA tank.
- Seat not included.

### Technology

- Dual-flush technology allows you to choose between a full or partial flush.

### Installation

- Standard 12" (305 mm) rough-in.
- Three-bolt quick-connect installation.

### Water Conservation & Rebates

- Eligible for consumer rebates in some municipalities.

### Recommended Products/Accessories

K-4639 Cachet® Quiet-Close™ Round-Front Toilet Seat  
K-5589 Purefresh® Round-Front Toilet Seat  
K-76923 Puretide™ Quiet-Close™ Round-front manual  
cleansing toilet seat  
K-5420 Low-Profile Bolt Caps  
K-9236 Trip Lever Dual Flush  
1023457 Wax Ring/Hardware Kit  
1265114 Connector Hose  
K-23726 Drain treatment

### Included Components

Product consists of:

K-4458-RA Toilet tank, dual-flush  
K-4197 Round-Front Bowl  
K-9236 Trip Lever Dual Flush

Additional Components:

Bolt cap accessory pack  
Bowl  
Tank  
Tank cover  
Trip lever



### Codes/Standards



ASME A112.19.2/CSA B45.1  
ASME A112.19.14  
EPA WaterSense®


### KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit



## Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece, Floor-mount
Waste Outlet:	Floor
Bowl shape:	Round-front
Flush type:	Class Five®
Trap passageway:	2-1/8" (54 mm)
Water Consumption	
Full:	1.6 gpf (6 lpf)
Reduced:	1.1 gpf (4.3 lpf)
Water surface size:	10-1/2" x 7-3/4" (267 mm x 197 mm)
Rim to water surface:	5-1/4" (133 mm)
Rough-in:	12" (305 mm)
Seat-mounting holes:	5-1/2" (140 mm)

## Notes

Install this product according to the installation instructions.

For back-to-back toilet installations: Use only a 45° double wye fitting.