

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0191640075**  
**Status:** **Active**  
**Overview:** Perma-Seal Terminals  
**Description:** Perma-Seal Male Quick Disconnect Tab for 10-12 AWG Wire, Tab Size 6.35 x 0.81mm, Bag

**Documents:**

Drawing (PDF) Product Specification PS-19902-013-001 (PDF)  
Product Specification PS-19902-011-001 (PDF) RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA LR18689  
 UL E79133

**General**

Product Family Quick Disconnects  
 Series 19164  
 Crimp Quality Equipment Yes  
 Insulated Fully  
 Overview Perma-Seal Terminals  
 Product Name Perma-Seal  
 Taxonomy Quick Disconnects  
 Type Quick Disconnect  
 UPC 800753113596

**Physical**

Barrel Type Closed  
 Color - Resin Yellow  
 Gender Male  
 Glow-Wire Capable No  
 Insulation NiAc  
 Lock to Mating Part None  
 Material - Metal Brass  
 Material - Plating Mating Zinc Chromate  
 Material - Plating Termination Zinc Chromate  
 Material - Resin Nylon  
 Net Weight 2.830/g  
 Orientation Straight  
 Packaging Type Bag  
 Tab Thickness 0.81mm  
 Tab Width 6.35mm  
 Temperature Range - Operating -55° to +125°C  
 Wire Insulation Diameter 5.84mm max.  
 Wire Size AWG 10, 12  
 Wire Size mm<sup>2</sup> 4.00-6.00

**Electrical**

Voltage - Maximum 600V

**Material Info**

Engineering Number SC-9280

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19164-039-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2022)4187-DC (10  
 June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

19164 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Hand Crimp Tool 640016100

This document was generated on 08/27/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**