

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0442420010

Status:

Active

Overview:

Micro-Fit Connector System

Description:

Micro-Fit 3.0 Test Plug, Dual Row, 22 Circuits



Documents:	
Drawing (PDF)	Product Specification 436500001-PS-SP-000 (PDF)
3D Model	Product Specification PS-43650-001 (PDF)
3D Model (PDF)	Packaging Specification PK-44242-001-001 (PDF)
Product Specification 436500001-PS-JA-000 (PDF)	Datasheet (PDF)
Product Specification 436500001-PS-KO-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	44242
Application	Signal, Wire-to-Board
Overview	Micro-Fit Connector System
Product Name	Micro-Fit 3.0
Taxonomy	PCB Headers and Receptacles
UPC	800754019958
Physical	
Breakaway	No
Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	10000
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Beryllium Copper
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	13.619/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	6.81mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Solder or Weld
Electrical	
Current - Maximum per Contact	2.5A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Contained Per -ED/01/2018 (15 January 2018)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

44242 Series

Mates With

Micro-Fit 3.0 Receptacle Housing 43025

 Micro-Fit BMI Panel Mount Receptacle Housing 44133

Reference - Drawing Numbers

Packaging Specification	PK-44242-001-001
Product Specification	436500001-PS-JA-000, 436500001-PS-KO-000, 436500001-PS-SP-000, PS-43650-001
Sales Drawing	SD-44242-001-001

This document was generated on 08/31/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION