

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0640018800](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for Avikrimp Fully Insulated and Insulated Quick Disconnect Flags, 10-12 AWG

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Avikrimp, N/A
Taxonomy	Crimp Presses and Crimp Hand T
Tool Type	Hand Crimp Tool
UPC	889056261234
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents [ATS-6400188HM-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[207129 Series](#)

Use With

Avikrimp Fully Insulated and Insulated Quick Disconnect Flags, 10-12 AWG

Application Tooling

FAQ

Description	Product #
-------------	-----------

Avikrimp Quick Disconnect, for 10-12 AWG Wire, Female Flag, Tab 6.35 x 0.81mm	190060019
---	---------------------------

Flag InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm ²) Wire, Box, Tab 6.35 x 0.81mm	190070040
--	---------------------------

InsulKrimp Female Fully Insulated Quick Disconnect Flag for 10-12 AWG Wire, Tab 6.35 x 0.81mm, 94 V-0 Material	190070082
--	---------------------------

This document was generated on 10/07/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION