

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008500106](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: [KK 396 Crimp Terminal 2478, 18-24 AWG, Bag, Brass Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001-001 \(PDF\)](#)
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [2478](#)
Application [Power, Wire-to-Board](#)
Crimp Quality Equipment [Yes](#)
Overview [KK Interconnect Systems](#)
Packaging Alternative [08500105 \(Reel\)](#)
Product Name [KK 396, KK 508](#)
Taxonomy [Crimp Terminals](#)
UPC [800753750029](#)

Physical

Gender [Female](#)
Material - Metal [Brass](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.280/g](#)
Packaging Type [Bag](#)
Plating min - Mating [2.540µm](#)
Plating min - Termination [2.540µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [2.79mm max.](#)
Wire Size AWG [18, 20, 22, 24](#)
Wire Size mm² [N/A](#)

Solder Process Data

Lead-freeProcess Capability [N/A](#)

Material Info

Engineering Number [2478-1-\(P909\)L](#)

Reference - Drawing Numbers

Packaging Specification [PK-2759-001-001](#)
Product Specification [PS-08-50-001](#)
Sales Drawing [SD-2478-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2478 Series](#)

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016
Hand Crimp Tool for 3.96mm Pitch KK Crimp Terminals, 18-24 AWG	638279500

Japan

Description

Product #

Hand Extraction Tool 11260059

Hand Extraction Tool 570926000

This document was generated on 10/13/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION