

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936012770

Status:

Active

Overview:

GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 16B «77x27», Extended Pg21 Thread, Grey

Documents:

RoHS Certificate of Compliance (PDF)

|                      |                                                         |
|----------------------|---------------------------------------------------------|
| Agency Certification |                                                         |
| CSA                  | 256883                                                  |
| UL                   | E249674                                                 |
| General              |                                                         |
| Product Family       | Industrial Connectors / Enclosures                      |
| Series               | 93601                                                   |
| Component Size       | 16B «77X27»                                             |
| Component Type       | Single Lever Hood                                       |
| IP Rating            | IP66                                                    |
| Overview             | GWconnect Heavy Duty Connectors (HDC)                   |
| Product Category     | Heavy Duty Connectors                                   |
| Product Name         | GWconnect                                               |
| Standard             | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Taxonomy             | Heavy-Duty Connectors                                   |
| Type                 | STD                                                     |
| UPC                  | 887191847849                                            |
| Physical             |                                                         |
| Entry Location       | Side                                                    |
| Hood Coating         | Polyester Powder                                        |
| Hood Color           | GREY RAL 7037                                           |
| Lock to Mating Part  | Yes                                                     |
| Material - Hood      | Die-cast Aluminum                                       |
| Material - Peg       | Stainless Steel                                         |
| Net Weight           | 147.200/g                                               |
| Number of Pegs       | 2                                                       |
| Packaging Type       | Bag                                                     |
| Thread Size          | Pg21                                                    |
| Thread Type          | (Pg)                                                    |
| Electrical           |                                                         |
| Voltage - Maximum    | 500V                                                    |
| Material Info        |                                                         |
| Engineering Number   | 7816.6507.0                                             |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2022)4187-DC (10 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT\_CE - Declaration of Conformity

CER\_4000400719\_00\_000.pdf

Search Parts in this Series

93601 Series

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION